

6ft (1.8m) Heavy Duty Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, NEMA 5-15R to NEMA 5-15P AC Power Cord - UL Listed

**Product ID:** PAC101146



The PAC101146 Power Cord Extension Cable features a heavy-duty wire gauge (14 AWG) that's suitable for handling higher power levels than typical cables, making it a reliable solution for connecting larger servers to PDUs (Power Distribution Units).

This high quality cable extends your existing power connection by 6ft, enabling you to use a PC or other powered device at a greater distance from the power source/outlet than would typically be possible.

This durable, replacement Power Extension Cable is backed by our Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Extend an existing power cord by an additional 6ft

## Features

- **HEAVY DUTY EXTENSION CORD:** This 6ft (1.8m) 14AWG universal power cord with NEMA 5-15R to NEMA 5-15P connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 15A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability  
Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths
- **SPECS:** 6ft (1.8m) AC Power Cord NEMA 5-15R to NEMA 5-15P 14AWG 125V 15A (Max) Jacket Type: SJT  
Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

#### Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

#### Performance

Maximum Cable Length	6.0 ft [1.8 m]
----------------------	----------------

#### Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

#### Special Notes / Requirements

Note	UL Listed
------	-----------

#### Power

Input Voltage	125 AC
Input Current	15A

#### Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.0 in [0.0 mm]

Product Height	0.0 in [0.0 mm]
Weight of Product	11.0 oz [311.0 g]

---

#### Packaging Information

Package Quantity	1
Package Length	9.1 in [23.1 cm]
Package Width	8.6 in [21.9 cm]
Package Height	2.2 in [5.6 cm]
Shipping (Package) Weight	10.9 oz [308.0 g]

---

#### What's in the Box

Included in Package	1 - 6 ft 14 AWG Power Cord Extension - NEMA 5-15R to NEMA 5-15P
---------------------	---

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***