

15ft (4.5m) Power Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

Produkt-ID: PAC10115



This 15-foot Computer Power Cord Extension Cable instantly turns a large, awkward power connector into a smaller, streamlined connector.

The power adapter will fit into any socket, maximizing the space on your power strip, surge protector, or wall outlet.

The power adapter also doubles as a power cord extender, giving you an extra 15ft of reach for your monitor, computer case, or any other powered device.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend an existing power cord by an additional 15ft
- Allows you to attach bulky power adapter to a power strip or a wall outlet without blocking other outlets

Merkmale

- **POWER EXTENSION CORD:** This 15ft (4.5m) 16AWG AC power extension cable with NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 13A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief on connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord with 100% copper wire | This cable is available in other lengths
- **SPECS:** 15ft (4.5m) AC Power Cord | NEMA 5-15R to NEMA 5-15P | 16AWG | 125V 13A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets | Extend a 3-prong power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen 2 Years

Kabeltyp SJT

Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)

Steckverbinder B 1 - NEMA 5-15 Strom (Nordamerika)

Strom

Eingangsspannung 125 AC

Eingangsstrom 13 A

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 16 AWG

Kabellänge 15.0 ft [4.6 m]

Produktlänge 15.0 ft [4.6 m]

Produktbreite	1.0 in [2.6 cm]
Produkthöhe	1.4 in [3.5 cm]
Produktgewicht	19.2 oz [543.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	8.9 in [22.6 cm]
Paketbreite	9.3 in [23.7 cm]
Pakethöhe	2.0 in [5.2 cm]
Versandgewicht (Verpackung)	1.3 lb [0.6 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 15 ft Power Cord Extension - NEMA 5-15R to NEMA 5-15P
--------------------	-----------------------------------------------------------

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.