


1 Port PCI Parallel Adapter Card

Product ID: PCI1P2



The PCI1P2 1-Port Parallel PCI Card adds one ECP/EPP/SPP/BPP IEEE 1284 port to your PC, with support for data transfer speeds of up to 1.8Mbps.

This versatile card offers compatibility with PCI or PCI-X expansion slots (3.3/5V, 32/64-bit), as well as a simple plug and play installation with support and drivers for a broad range of operating systems including Windows 7, Server 2008 R2, XP Embedded DOS, Linux and more. The PCI Parallel card also features IRQ sharing and hot swapping capabilities, which guarantee convenient, hassle-free connections to any parallel peripheral.

This product is a replacement for our PCI1P card.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connecting any parallel peripheral including printers, scanners, CD-R/RWs, Zip drives, and memory card readers to a computer, through PCI/PCI-X

Features

- Supports EPP, ECP, SPP and BPP
- Data transfer rates of up to 1.8Mbps
- Supports both 64-bit PCI-X & 32-bit PCI slots

- Easy plug and play installation with I/O address and IRQ assigned by system
- Support for Microsoft Windows, Linux, and DOS

Hardware

Warranty	Lifetime
Ports	1
Interface	Parallel
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile
Port Style	Integrated on Card
Regulatory Approvals	EN55022 Class B, EN55024, EN61000-3-2, EN61000-3-3,FCC Part 15 Class B, RoHS
Industry Standards	IEEE-1284, PCI Ver 3.0, 2.3, 2.2, 2.1
Chipset ID	Sunix - SUN1989

Performance

Maximum Data Transfer Rate	1.8Mbps
FIFO	16 Byte
Supported Protocols	BPP, ECP, EPP, SPP


Connector(s)

Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
External Ports	DB-25 (25 pin, D-Sub)

Software

OS Compatibility	Windows DOS, 95, 98SE, NT, ME, XP Embedded, POS Ready 2009, Embedded System 2009, XP, Vista, 7, 8, 8.1 Windows Server 2000, 2003, 2008 R2, 2012, 2012 R2 Linux 2.4.x / 2.6.x
Microsoft WHQL Certified	Yes

Special Notes / Requirements



System and Cable Requirements	PC with an available PCI/PCI-X slot
-------------------------------	-------------------------------------

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	5~95% RH

Physical Characteristics

Product Length	4.8 in [12.1 cm]
Product Width	0.6 in [14 mm]
Product Height	2.5 in [63 mm]
Weight of Product	1.7 oz [48 g]

Packaging Information

Package Length	6.7 in [17 cm]
Package Width	5.5 in [14 cm]
Package Height	1.3 in [32 mm]
Shipping (Package) Weight	4.9 oz [140 g]

What's in the Box

Included in Package	PCI Parallel Card
	Driver CD
	User Manual

**Product appearance and specifications are subject to change without notice.*

