

6ft (2m) Power Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

Produkt-ID: PAC1016



The PAC1016 power extension cord extends your existing power connection by up to 6ft.

The added cable distance allows you to minimize clutter, giving you more room for additional connections on your power strip, surge protector or wall outlet.

Designed for durability and dependability, this NEMA extension cord is backed by our Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend the connection distance between your PC, Monitor, Laser Printer or Scanner and your power strip, surge protector or wall outlet by up to 6 ft

Merkmale

- POWER EXTENSION CORD: This 6ft (2m) 16AWG AC power extension cable with NEMA 5-15R and

NEMA 5-15P connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 13A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief on connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord with 100% copper wire | This cable is available in other lengths
- **SPECS:** 6ft (2m) AC Power Cord | NEMA 5-15R to NEMA 5-15P | 16AWG | 125V 13A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets | Extend a 3-prong power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SJT

Leistung

Max. Kabellänge	6.0 ft [1.8 m]
-----------------	----------------

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - NEMA 5-15 Strom (Nordamerika)

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	13A

Physische
Eigenschaften

Farbe	Schwarz
Drahtstärke	16 AWG
Kabellänge	6.0 ft [1.8 m]
Produktlänge	6.0 ft [1.8 m]
Produktgewicht	8.6 oz [245 g]

Verpackungsinform
ationen

Paketmenge	1
Paketlänge	4.9 in [12.5 cm]
Paketbreite	7.8 in [19.8 cm]
Pakethöhe	2.0 in [5.2 cm]
Versandgewicht (Verpackung)	8.8 oz [248.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 6ft Power Cord Extension - NEMA 5-15R to NEMA 5-15P
--------------------	---

Garantieinformatio
nen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.