


3 Port PCI Low Profile High Speed USB 2.0 Adapter Card

Produkt ID: PCI220USBLP



This 3-Port PCI USB 2.0 Adapter Card adds two external USB 2.0 ports as well as one internal USB 2.0 port, through simple installation in a single PCI slot.

The PCI USB 2.0 card supports plug and play installation as well as hot-swappable connectivity with USB 2.0 devices, ensuring convenient, hassle-free connections without having to reboot the computer.

The 3-port PCI USB 2.0 adapter card features a low-profile design that's suited for small form factor cases and is backed by StarTech.com's Lifetime Warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Expand a low profile/small form factor PCI-based system's USB capabilities with two additional external USB ports
- Add additional USB bandwidth to a system that already uses many USB devices/hubs

- Connect additional external hard drives, CD/DVD drives, MP3 players, printers, scanners, webcams, game controllers, digital cameras, etc. to a computer system

Funktioner

- Ger två externa USB 2.0-portar och en delad intern port
- Fullständigt kompatibel med USB 2.0-specifikationerna, med stöd för överföringshastigheter på upp till 480 Mbps
- Bakåtkompatibel med USB 1.0/1.1-enheter
- Uppfyller den reviderade PCI 2.2-specifikationen
- Stöder upp till 127 USB-enheter per port (flera USB-hubbar krävs)
- Plug-and-play- och hot-swap-kompatibel

Hårdvara

Garantipolicy	Lifetime
Portar	2
Gränssnitt	USB 2.0
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Lågprofil
Chipset-ID	VIA/VLI - VT6212

Prestanda

Maximal dataöverföringshastighet	480 Mbps
----------------------------------	----------

Kontakt(er)

Kontakttyp(er)	1 - PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
Interna portar	1 - USB 2.0 Type-A (4 stift, 480 Mbps)
Externa portar	2 - USB 2.0 Type-A (4 stift, 480 Mbps)

Mjukvara

OS-kompatibilitet	Windows® 2000, XP
-------------------	-------------------

		.Linux 3.5.x till 4.11.x endast LTS-versioner
	Microsoft WHQL-certifierad	Ja
Särskilda anmärkningar/krav	Obs.	PCI220USBLP allows for all ports including internal to be used simultaneously
Utseende	Produktlängd	5.0 in [12.7 cm]
	Produktbredd	0.8 in [2 cm]
	Produkthöjd	3.1 in [8 cm]
	Produktvikt	3.5 oz [100 g]
Förpackning	Förpackningsantal	1
	Paketets längd	6.8 in [17.2 cm]
	Paketets bredd	2.7 in [68 mm]
	Paketets höjd	7.1 in [18 cm]
	Fraktvikt (förpackning)	0.2 lb [0.1 kg]
Vad det är i lådan	Ingår i paketet	1 - PCI USB-kort med låg profil 1 - Instruktionsbok
Warranty Information	Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.