


1 Port eSATA + 1 Port SATA PCI SATA Controller Card w/ LP Bracket

Produkt ID: PCIESATA2I



This PCI based SATA Controller Card allows you to turn a PCI slot into one internal SATA and one external SATA (eSATA) connection. Supporting SATA 150 hard drives, and data transfer rates of up to 1.5Gbps, this controller card is the perfect solution if you need an extra SATA port or want to externalize your storage.

Certifikat, rapporter och kompatibilitet

Användning

- Upgrade a PCI-based desktop with SATA and eSATA capabilities
- Add additional SATA capabilities to a desktop computer
- Add SATA capabilities to a low profile/small form factor (SFF) computer

Funktioner

- 1 internal SATA port and 1 external eSATA port
- Large capacity drive support with 48-bit Logical Block Addressing (LBA)
- Fully compliant with the Serial ATA 1.0a specification, with transfer rates up to 1.5Gbps
- Independent 256-byte FIFOs (32 bit x 64 deep) per SATA channel

- Integrated PCI DMA engines
- Includes a low profile/half-height installation bracket

Hårdvara

Garantipolicy	2 Years
Portar	2
Gränssnitt	SATA eSATA & SATA
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil (inkl. LP-fäste)
Chipset-ID	VIA/VLI - VT6421

Prestanda

Maximal dataöverföringshastighet	1.5 Gb/sec
Typ och hastighet	SATA 1.5 Gbit/s (SATA I)
Port Multiplier	Nej
RAID	Nej

Kontakt(er)

Kontakttyp(er)	PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
Interna portar	SATA (7-stifts, data)
Externa portar	eSATA (7-stifts, data)

Mjukvara

OS-kompatibilitet	Windows® 2000, XP, Vista, 7, 8 Windows Server® 2003, 2008 R2 Linux 3.5.x to 4.11.x <i>LTS Versions only</i>
-------------------	---

Utseende

Kabinetttyp	Stål
-------------	------

Produktlängd	4.8 in [12.1 cm]
Produktbredd	2.1 in [54 mm]
Produkt höjd	0.8 in [20 mm]
Produktvikt	1.6 oz [46.6 g]

Förpackning

Förpackningsantal	1
Package Length	6.9 in [17.5 cm]
Package Width	5.6 in [14.2 cm]
Package Height	1.2 in [30 mm]
Fraktvikt (förpackning)	4.8 oz [135 g]

Vad det är i lådan

Ingår i paketet	PCI eSATA Card
	Low Profile Bracket
	SATA Data Cable
	Software CD
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

