

## 1 Port Low Profile PCI Parallel Adapter Card

**Product ID:** PCI1P\_LP

The PCI1P\_LP 1 Port Low Profile PCI Parallel Adapter Card adds one IEEE 1284 port to your small form factor PC, with data transfer speeds of up to 1.5 Mbps – up to 3 times faster than on-board parallel ports. The adapter card features a low profile design that is suited to small form factor computer cases, while including a full height bracket to adapt to any installation.

Installation is a breeze with plug and play support and drivers for Windows 7, Vista, XP, ME, 2000, 98, 95, NT4, DOS and Linux. IRQ sharing and hot swapping capabilities guarantee convenient, hassle-free connections to any parallel peripheral.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip drives, and memory card readers

## Features

- Easy plug and play installation
- Data transfer rates of up to 1.5 Mbps
- IRQ sharing eliminates conflicts between multiple cards
- Supports EPP, ECP, SPP and BPP
- Compatible with low profile systems
- Installation scripts available for Linux RedHat 7.2, SuSE 7.3 and Mandrake 8.2

Hardware	Warranty	Lifetime
	Ports	1
	Interface	Parallel
	Bus Type	PCI / PCI-X (5 / 3.3V)
	Card Type	Low Profile (SP bracket incl.)
	Port Style	Integrated on Card
	Industry Standards	PCI 2.1
	Industry Standards	EPP
	Industry Standards	ECP
	Industry Standards	SPP

	Industry Standards	BPP
	Chipset ID	ASIX - MCS9805CV
<b>Performance</b>	Maximum Data Transfer Rate	1.5 Mbps
<b>Connector(s)</b>	Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
	External Ports	DB-25 (25 pin, D-Sub)
<b>Software</b>	OS Compatibility	Windows DOS, 95, 98SE, ME, XP, Vista, 7, 8, 8.1, 10 Linux 3.5.x to 4.11.x <i>LTS Versions only</i>
<b>Special Notes / Requirements</b>	System and Cable Requirements	Unused PCI slot
<b>Physical Characteristics</b>	Material	Steel
	Product Length	4.7 in [1.2 cm]
	Product Width	0.8 in [20.000 mm]
	Product Height	2.2 in [55.000 mm]
	Weight of Product	1.7 oz [49.000 g]
<b>Packaging Information</b>	Package Length	5.7 in [1.4 cm]
	Package Width	6.9 in [1.8 cm]
	Package Height	1.2 in [31.000 mm]
	Shipping (Package) Weight	4.7 oz [132.000 g]
<b>What's in the Box</b>	Included in Package	Low Profile PCI Parallel Card
	Included in Package	Driver CD
	Included in Package	Manual
	Included in Package	Standard profile bracket

***\*Product appearance and specifications are subject to change without notice.***

