

1 Port PCI Dual Voltage Parallel Adapter Card

Produkt ID: PCI1PECPDV



The PCI1PECPDV PCI Dual Voltage EPP/ECP Parallel Adapter Card adds an IEEE 1284 port to your PC using either a PCI 5V or PCI-X 3.3v slot, with support for data transfer speeds of up to 1.5 Mbps – up to 3 times faster than built-in parallel ports.

The adapter card supports a broad range of operating systems including Windows®, DOS® and Linux® for easy installation into mixed environments. Plus, IRQ sharing and plug and play capabilities guarantee convenient, hassle-free connections to any parallel peripheral.

This PCI Parallel adapter card is a complete dual profile solution, providing both a standard bracket and a low profile/half-height bracket for adapting to slimline or small form-factor system applications.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory

card readers

Funktioner

- Supports 3.3 and 5V PCI slots
- Maximum data transfer rate of 1.5 Mbps
- Standard and low-profile bracket included
- IRQ sharing eliminates conflicts between multiple cards
- PCI 2.2 and PCI Power Management 1.0 compliant
- SPP/EPP/ECP Parallel port that fully supports existing Centronics interface

Hårdvara

Garantipolicy	Lifetime
Portar	1
Gränssnitt	Parallell
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil (inkl. LP-fäste)
Porttyp	Inbyggd på kort
Chipset-ID	PLX/Oxford - OX16PCI952

Prestanda

Maximal dataöverföringshastighet	1.5 Mbps
----------------------------------	----------

Kontakt(er)

Kontakttyp(er)	1 - PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
Externa portar	1 - DB-25 (25-stifts, D-Sub)

Mjukvara

OS-kompatibilitet	Windows® 8 (32/64), 7 (32/64), Vista (32/64), XP (32/64), 2000, ME, 98SE, 95 Windows Server® 2012, 2008 R2
-------------------	---

Linux 2.4.x and up

Utseende

Produktlängd	4.7 in [12 cm]
Produktbredd	0.8 in [2 cm]
Produkthöjd	4.7 in [12 cm]
Produktvikt	2.1 oz [60 g]

Förpackning

Paketets längd	5.8 in [14.8 cm]
Paketets bredd	2.3 in [58 mm]
Paketets höjd	7.7 in [19.5 cm]
Fraktvikt (förpackning)	0.3 lb [0.1 kg]

Vad det är i lådan

Ingår i paketet	1 - PCI Parallel Card
	1 - Low Profile Bracket
	1 - Driver CD
	1 - Instruction Manual

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.