


## 5 Port PCI High Speed USB 2.0 Adapter Card

Product ID: PCI420USB



This PCI-based High Speed USB 2.0 Adapter Card adds five USB 2.0 'A' Female ports (1 internal, 4 external) to your PCI-capable PC.

Supported by popular operating systems including Windows 98SE/ME/2000/XP/Vista, the PCI USB 2.0 card is a versatile solution that lets you add USB 2.0 connections without having to upgrade the system motherboard.

A convenient and time-saving solution, the PCI USB card is WHQL certified to simplify driver installation in Windows XP operating environments, and supports USB device hot-swapping - allowing you to connect/disconnect USB peripherals without having to power down the computer.

Designed and constructed to provide long-lasting USB capability, the adapter card is backed by StarTech.com's Lifetime Warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Expand a PCI-based system's USB capabilities with four additional external USB ports
- Add additional USB bandwidth to a system that already uses many USB devices/hubs
- Connect additional external hard drives, CD/DVD drives, MP3 players, printers, scanners, webcams, game controllers, digital cameras, etc. to a computer system

### Features

- Provides four external USB 2.0 ports and one shared internal port

- Fully compliant with USB 2.0 specifications, with support for transfer rates up to 480 Mbps
- Backwards compatible with USB 1.0/1.1 devices
- Compliant with PCI revision 2.2 specification
- Supports up to 127 USB devices per port (requires additional USB hubs)
- Plug-and-Play and Hot-Swap compatible

<b>Hardware</b>	Warranty	Lifetime
	Ports	5
	Interface	USB 2.0
	Bus Type	PCI / PCI-X (5 / 3.3V)
	Card Type	Standard Profile
	Industry Standards	OHCI
	Industry Standards	EHCI
	Industry Standards	PCI 2.2
	Chipset ID	VIA/VLI - VT6212
<b>Performance</b>	Maximum Data Transfer Rate	480 Mbps
<b>Connector(s)</b>	Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
	Internal Ports	USB Type-A (4 pin) USB 2.0
	External Ports	USB Type-A (4 pin) USB 2.0
<b>Software</b>	OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10
	Microsoft WHQL Certified	Windows Server 2008 R2, 2012, 2016
		Mac OS X 10.6 to 10.10
		Linux 3.5.x to 4.11.x <i>LTS versions only</i>
	Yes	
<b>Special Notes / Requirements</b>	System and Cable Requirements	Unused PCI slot
	Note	The internal USB 2.0 is shared with the top-most external USB 2.0 port, therefore only one of those ports may be used at a time.
<b>Environmental</b>	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 85C (-40F to 185F)
	Humidity	10~90% RH
<b>Physical</b>	Product Length	4.7 in [1.2 cm]

**Characteristics**

Product Height	3.7 in [95 mm]
Weight of Product	1.1 oz [30 g]

---

**Packaging Information**

Package Length	8.3 in [2.1 cm]
Package Width	1.7 in [42 mm]
Package Height	5.7 in [1.4 cm]
Shipping (Package) Weight	3.9 oz [110 g]

---

**What's in the Box**

Included in Package	PCI USB card
Included in Package	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

