


2 Port PCI SuperSpeed USB 3.0 Card Adapter

Produkt ID: PCIUSB3S2



The PCIUSB3S2 2-Port PCI to SuperSpeed USB 3.0 Card allows for legacy PCI slots to support the USB 3.0 standard, which is capable of data transfer rates up to 5 Gbps (10x faster than USB 2.0). Using USB 3.0 devices with this Card will allow data transfer rates at up to 1.3 Gbps, double the performance versus using USB 2.0 cards and peripherals.

Backward compatible with USB 2.0 and 1.x devices, this versatile PCI USB 3.0 card will work with any future USB 3.0 devices, while still being able to support older devices.

Designed for older PCI-based systems or computers with only PCI expansion slots left available, this adapter card allows those systems to stay relevant and up-to-date with the latest USB technology.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Add USB 3.0 capabilities to an older PCI-based system
- Expand system capabilities with additional external USB ports
- Enable high speed USB 3.0 data communication for external storage devices and audio/video devices

Funktioner

- 2 external USB 3.0 ports
- SuperSpeed USB 3.0 compliant host connection
- Provides up to 900mA of power over USB
- Compliant with USB 3.0 base specification 1.0 and xHCI specification 0.95
- Backward compatible with USB 2.0/1.x devices
- Compliant with PCI Local Bus specification 3.0
- Support for up to 127 USB devices per port (requires additional USB hubs)
- Configured with a Full Profile installation bracket and includes optional Low Profile bracket

Hårdvara

Garantipolicy	Lifetime
Portar	2
Gränssnitt	USB 3.0
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil (inkl. LP-fäste)
Chipset-ID	Renesas/NEC - μ PD720200

Prestanda

Maximal dataöverföringshastighet	1.3 Gbps (PCI Bus)
UASP-stöd	Nej

Kontakt(er)

Kontakttyp(er)	PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
Interna portar	LP4 (4-stift, Molex-type Large Drive Power)
Externa portar	USB Type-A (9-stifts) USB 3.0 (5 Gbps)

Mjukvara

OS-kompatibilitet	Windows XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)/ 8(32/64-bit)
-------------------	---



Särskilda
anmärkningar/krav

System- och kabelkrav Available PCI expansion slot

Miljö

Drifttemperatur 5°C to 50°C (41°F to 122°F)
Förvaringstemperatur -25°C to 70°C (-13°F to 158°F)
Luftfuktighet 15% ~ 90% RH

Utseende

Produktlängd 4.7 in [12 cm]
Produktbredd 4.7 in [12 cm]
Produkthöjd 0.8 in [20 mm]
Produktvikt 1.9 oz [54 g]

Förpackning

Package Length 6.9 in [17.5 cm]
Package Width 5.5 in [14 cm]
Package Height 1.2 in [30 mm]
Fraktvikt (förpackning) 5.1 oz [145 g]

Vad det är i lådan

Ingår i paketet
PCI USB 3.0 card
Low Profile Bracket
Driver CD
Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

