


## 2 Port PCI SuperSpeed USB 3.0 Card Adapter

**Product ID:** PCIUSB3S2



The PCIUSB3S2 2-Port PCI to SuperSpeed USB 3.0 Card allows for legacy PCI slots to support the USB 3.0 standard, which is capable of data transfer rates up to 5 Gbps (10x faster than USB 2.0). Using USB 3.0 devices with this Card will allow data transfer rates at up to 1.3 Gbps, double the performance versus using USB 2.0 cards and peripherals.

Backward compatible with USB 2.0 and 1.x devices, this versatile PCI USB 3.0 card will work with any future USB 3.0 devices, while still being able to support older devices.

Designed for older PCI-based systems or computers with only PCI expansion slots left available, this adapter card allows those systems to stay relevant and up-to-date with the latest USB technology.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Add USB 3.0 capabilities to an older PCI-based system
- Expand system capabilities with additional external USB ports
- Enable high speed USB 3.0 data communication for external storage devices and audio/video devices

### Features

- 2 external USB 3.0 ports

- SuperSpeed USB 3.0 compliant host connection
- Provides up to 900mA of power over USB
- Compliant with USB 3.0 base specification 1.0 and xHCI specification 0.95
- Backward compatible with USB 2.0/1.x devices
- Compliant with PCI Local Bus specification 3.0
- Support for up to 127 USB devices per port (requires additional USB hubs)
- Configured with a Full Profile installation bracket and includes optional Low Profile bracket

---

#### Hardware

Warranty	Lifetime
Ports	2
Interface	USB 3.0
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile (LP bracket incl.)
Chipset ID	Renesas/NEC - PD720200

---

#### Performance

Maximum Data Transfer Rate	1.3 Gbps (PCI Bus)
UASP Support	No

---

#### Connector(s)

Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
Internal Ports	LP4 (4 pin; Large Drive Power)
External Ports	USB Type-A (9 pin) USB 3.0 (5 Gbps)

---

#### Software

OS Compatibility	Windows XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)/ 8(32/64-bit)
------------------	---

---

#### Special Notes / Requirements

System and Cable Requirements	Available PCI expansion slot
-------------------------------	------------------------------



---

**Environmental**

Operating Temperature	5C to 50C (41F to 122F)
Storage Temperature	-25C to 70C (-13F to 158F)
Humidity	15% ~ 90% RH

---

**Physical Characteristics**

Product Length	4.7 in [12 cm]
Product Width	4.7 in [12 cm]
Product Height	0.8 in [20 mm]
Weight of Product	1.9 oz [54 g]

---

**Packaging Information**

Package Length	6.9 in [17.5 cm]
Package Width	5.5 in [14 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	5.1 oz [145 g]

---

**What's in the Box**

Included in Package	PCI USB 3.0 card
	Low Profile Bracket
	Driver CD
	Instruction Manual

---

*\*Product appearance and specifications are subject to change without notice.*

