


4 Channel Low Profile PCI Sound Adapter Card AC97 3D Audio Effects

Product ID: PCISOUND4LP



This PCI sound card provides high quality, multi-channel audio capability and is configured with low profile bracket that allows the card to be installed in a slim form factor or low profile PC case.

The sound card includes a microphone port for applications requiring audio input (voice chat etc.), two audio output ports for rich, clear sound, and a Line-In port for simple connection of auxiliary devices.

Certifications, Reports and Compatibility

Applications

- Replace failed or stereo-only onboard audio for a small form factor or full desktop system
- Upgrade to 5.1 audio for a desktop without onboard audio or less than 5.1 surround
- Build a inexpensive home theater PC or multimedia PC with surround sound capabilities

Features

- 4 channel audio output via 3.5mm mini-jacks
- Support for EAX, Karaoke Key and Echoing
- Built-in 32 Ohm earphone buffer
- Full-Duplex operation for recording and playback
- Supports up to 48KHz/16-bit sampling rates

- Legacy SBPro and DOS support
- Compliant with PCI revision 2.2 specification
- Low/Full Profile installation brackets included

Hardware

| | |
|--------------------|--------------------------------|
| Warranty | Lifetime |
| Bus Type | PCI (5 Volt) |
| Card Type | Low Profile (SP bracket incl.) |
| Industry Standards | PCI 2.2 Compliant |
| Chipset ID | C-Media - CMI8738-SX |

Performance

| | |
|----------------------|---|
| Audio Specifications | Supports 4 Channel 16 bit stereo audio |
| | Input/Output Connectors |
| | 2 output (front and rear), 1 Microphone, 1 Line In(Aux) |
| Full Duplex Support | Yes |

Connector(s)


| | |
|-------------------|----------------------------------|
| Connector Type(s) | PCI (5V, 32-bit) |
| Internal Ports | MPC2 (4 pin, Audio) |
| | IDC (10 pin, Motherboard Header) |
| External Ports | 3.5 mm Mini-Jack (3 Position) |

Software

| | |
|------------------|---|
| OS Compatibility | Windows 7 (32/64bit), Vista (32/64), XP (32/64), 2000 |
| | Windows Server 2008 R2, 2003 |
| | Linux |

Special Notes / Requirements

| | |
|------|------------------------------|
| Note | Standard Bracket is included |
|------|------------------------------|



Physical Characteristics

| | |
|-------------------|------------------|
| Product Length | 4.8 in [12.1 cm] |
| Product Width | 3.1 in [80 mm] |
| Product Height | 0.7 in [18 mm] |
| Weight of Product | 1.8 oz [50 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 6.9 in [17.4 cm] |
| Package Width | 1.2 in [30 mm] |
| Package Height | 5.6 in [14.2 cm] |
| Shipping (Package) Weight | 4.9 oz [140 g] |

What's in the Box

| | |
|---------------------|--------------------------|
| Included in Package | 4-channel PCI Sound Card |
| | Full profile Bracket |
| | Driver CD |
| | Instruction Manual |

****Product appearance and specifications are subject to change without notice.***

