

## 1 Port PCI Express Low Profile Parallel Adapter Card - SPP/EPP/ECP

**Product ID:** PEX1PLP



The PEX1PLP PCIe Parallel Adapter card can be installed in a PCI Express (PCIe) x1 slot, allowing you to connect EPP/ECP parallel peripherals to any computer, while relying on a native, single-chip design (Oxford OXPCIe952) that harnesses the capability of true PCI Express - ensuring maximum performance and reliability.

This high performance SPP/EPP/ECP parallel card adds 1 DB25 parallel port, perfect for connecting printers, scanners, CD-R/RW drives, memory card readers, bar code scanners and more. With the added convenience of plug-and-play capability, installing the parallel adapter card is hassle-free! The PCIe Parallel card also includes both standard and half-height/low profile mounting brackets for compatibility with almost any system form factor.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connects any parallel-based peripheral to your PC, including printers, scanners, CD-R/RWs, Zip drives, and memory card readers

### Features

- Compliant with PCI Express Base Specification 1.1a
- SPP/EPP/ECP Parallel port fully supports existing Centronics interface
- Packaged with low profile/half-height bracket attached, includes full profile bracket
- Compliant with PCI Power Management 1.2

---

**Hardware**

Warranty	2 Years
Ports	1
Interface	Parallel
Bus Type	PCI Express
Card Type	Low Profile (SP bracket incl.)
Port Style	Integrated on Card
Chipset ID	PLX/Oxford - OXPCle952

---

**Performance**

Maximum Data Transfer Rate	Up to 2.5Mbps
----------------------------	---------------

---

**Connector(s)**

Connector Type(s)	PCI Express x1
External Ports	DB-25 (25 pin, D-Sub)

---

**Software**

OS Compatibility	Windows CE 6.0 / 5.0, 95, 98SE, 2000, XP, XP Embedded, Vista, 7, 8, 8.1, 10  Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019  Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
------------------	--

---

**Environmental**

Operating Temperature	0C 50C (32F to 122F)
Storage Temperature	-20C 60C (-4F to 140F)
Humidity	5~85% RH

---

**Physical Characteristics**

Material	Steel
Product Length	0.8 in [21 mm]
Product Width	4.3 in [11 cm]



Product Height	4.7 in [12 cm]
Weight of Product	1.3 oz [37 g]

---

**Packaging Information**

Package Length	6.7 in [17 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	4.7 oz [133 g]

---

**What's in the Box**

Included in Package	Driver CD
	Instruction Manual
	Full Profile Bracket
	Low profile PCI Express Parallel Card

---

***\*Product appearance and specifications are subject to change without notice.***

