


7 Port PCI USB Card Adapter - TAA

Product ID: PCIUSB7



This PCI USB card adds seven USB 2.0 ports (1 internal USB A Female, 2 internal USB motherboard header, and 4 external USB A Female) to your PCI-capable PC.

The PCI USB 2.0 card is a versatile solution that lets you add USB 2.0 connections without having to upgrade the system motherboard.

An all-in-one solution, the PCI USB card supports USB 2.0 device connections for full data transfer speeds of up to 480Mbps, and is backward compatible with USB 1.1 devices (max. transfer rate 12Mbps), allowing you to connect any USB device to the computer without having to worry about compatibility issues.

Designed and constructed to provide long-lasting USB capability, the adapter card is backed by StarTech.com's free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add additional internal and external USB 2.0 ports to a desktop computer system
- Add an internal USB 2.0 header for use with internal/front-bay mounted USB peripherals
- Balance the number of available internal and external USB 2.0 ports on a computer system

Features

- 4 external USB 2.0 ports and 3 internal USB 2.0 port/headers
- High Speed USB 2.0 compliant, with support for data transfer rates up to 480Mbps
- Backwards compatible with USB1.1/1.0 devices
- Up to 500mA of power per port
- Compliant with USB EHCI revision 0.95 and UHCI 1.1 specifications
- Compliant with PCI revision 2.2 specification
- Supports up to 127 USB devices (requires addition USB hubs)
- Plug-and-Play and Hot-Swap compatible

Hardware

Warranty	2 Years
Ports	7
Interface	USB 2.0
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile
Industry Standards	EHCI 2.0
	OHCI 1.1
	Power Management 1.1
	PCI 2.2
Chipset ID	VIA/VLI - VT6212

Performance

Maximum Data Transfer	480 Mbps
-----------------------	----------

Rate

Connector(s)

Connector Type(s)	1 - PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
Internal Ports	1 - USB 2.0 Type-A (4 pin, 480Mbps) 1 - IDC (10 pin, Motherboard Header)
External Ports	4 - USB 2.0 Type-A (4 pin, 480Mbps)

Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022 Mac OS X 10.6 to 10.10 Linux 3.5.x and up - LTS Versions only
Microsoft WHQL Certified	Yes

Special Notes / Requirements

System and Cable Requirements	Unused PCI slot
-------------------------------	-----------------

Physical Characteristics

Color	Green
Material	Steel
Product Length	4.8 in [12.2 cm]
Product Width	4.7 in [12.0 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	2.6 oz [75.0 g]

Packaging Information

Package Quantity	1
Package Length	6.9 in [17.4 cm]
Package Width	5.6 in [14.3 cm]
Package Height	1.3 in [3.3 cm]

Shipping (Package) Weight	5.2 oz [146.0 g]
------------------------------	------------------

What's in the Box

Included in Package	1 - PCI USB 2.0 Card
	1 - Driver CD
	1 - Instruction Manual

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***