


5 Port PCI Express USB 2.0 Adapter Card

Product ID: PEX400USB2



This 5 Port PCI Express USB 2.0 Adapter Card lets you connect up to five USB 2.0 peripherals (4 external and shared 1 internal) to your computer, with support for high speed USB data transfer rates of up to 480 Mbps.

Plus, the PCI Express USB card is backward compatible with USB 1.1, so you can continue using your older USB peripherals.

Featuring easy plug and play installation, this adapter card provides convenient, hassle-free connections without having to reboot the host computer.

This product is backed by StarTech.com's Lifetime Warranty and FREE LIFETIME technical support.

Certifications, Reports and Compatibility

Applications

- Expand a system's USB capabilities with four additional external USB ports
- Add additional USB bandwidth to a system that already uses many USB devices
- Connect additional external hard drives, CD/DVD drives, MP3 players, printers, scanners, webcams, game controllers, digital cameras, etc. to a computer system

Features

- Provides four external USB 2.0 ports and one shared internal port
- Fully compliant with USB 2.0 specifications, with transfer rates up to 480 Mbps

- Backwards compatible with USB 1.0/1.1 devices
- Supports up to 127 USB devices per port (requires additional USB hubs)
- Plug-and-Play and Hot-Swap compatible

Hardware

Warranty	Lifetime
Ports	5
Interface	USB 2.0
Bus Type	PCI Express
Card Type	Standard Profile
Industry Standards	PCI Express One Lane 2.5Gb/s
Chipset ID	Renesas/NEC - D720101GU

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector Type(s)	PCI Express x1
Internal Ports	USB Type-A (4 pin) USB 2.0
External Ports	USB Type-A (4 pin) USB 2.0

Software

OS Compatibility	Windows 8 / 8.1 (32/64bit), 7 (32/64), Vista (32/64), XP (32/64), 2000 Windows Server 2012, 2008 R2, 2003
------------------	--

Special Notes / Requirements

System and Cable Requirements	Pentium II class or better CPU Unused PCI slot Windows 98SE or better
-------------------------------	---

Environmental



Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-50C to 150C (-5F to 302F)
Humidity	5~95% RH

Physical Characteristics

Product Length	3.4 in [87 mm]
Product Width	3.1 in [80 mm]
Product Height	0.4 in [9.6 mm]
Weight of Product	2.1 oz [59 g]

Packaging Information

Package Length	8.3 in [21 cm]
Package Width	1.5 in [38 mm]
Package Height	5.6 in [14.2 cm]
Shipping (Package) Weight	6.4 oz [180 g]

What's in the Box

Included in Package	PCI Express USB 2.0 card
	Instruction Manual

**Product appearance and specifications are subject to change without notice.*

