


1 Port PCI Express eSATA II Controller Card

Produkt ID: PEXESATA1



This eSATA Controller Card turns a PCI Express (1x) slot into an external SATA port, to provide a quick and hassle-free external storage solution.

Supporting SATA 300 (SATA II) hard drives (backward compatible with SATA /150) and data transfer rates of up to 3Gbps, this PCI Express eSATA Controller Card is the perfect solution for upgrading existing eSATA capability, or simply adding an external SATA port to a PC desktop computer.

Using a native PCI Express single chipset, the controller card provides enhanced compatibility, reliability and performance for your external storage needs. The controller card also features Port Multiplier support with command based switching for connecting multiple external hard drives to a host computer through one eSATA connection.

The PCI Express eSATA Controller Card also features an internal SATA port, which could be used for a conventional (internal) SATA drive installation. Please note that the internal SATA port can not be used at the same time as the external SATA port.

Certifikat, rapporter och kompatibilitet

Användning

- Provides you with one external eSATA port for connecting SATA devices such as external hard drive storage

Funktioner

- Selectable 1 external eSATA or 1 internal SATA port
- Support for FIS-based Port Multiplier technology
- Large capacity drive support with 48-bit Logical Block Addressing (LBA)
- Drive Hot-Plugging support
- Support for Native Command Queuing (NCQ)
- Fully compliant with the Serial ATA 1.0 specifications with support for transfer rates up to 3.0Gbps
- Uses native PCI Express single chipset
- Full/Low Profile installation brackets included

Hårdvara

Garantipolicy	Lifetime
Portar	1
Gränssnitt	eSATA
Busstyp	PCI Express
Korttyp	Standardprofil (inkl. LP-fäste)
Chipset-ID	Silicon Image - SiI3531

Prestanda

Maximal dataöverföringshastighet	3 Gbps
Typ och hastighet	SATA 3 Gbit/s (SATA II)
Port Multiplier	Ja
RAID	Nej
RAID-lägen som stöds	JBOD - (Just a Bunch of Disks)

Kontakt(er)

Kontakttyp(er)	PCI Express x1
Interna portar	SATA (7-stifts, data)



Externa portar eSATA (7-stifts, data)

Mjukvara

OS-kompatibilitet Windows® 2000, XP, Vista, 7, 8, 8.1
Windows Server® 2003, 2008 R2, 2012
Linux 2.6.x to 4.4.x <i>LTS Versions only</i>

Utseende

Produktlängd 4.7 in [12 cm]
Produktbredd 2.8 in [70 mm]
Produkthöjd 0.8 in [20 mm]
Produktvikt 1.3 oz [37 g]

Förpackning

Förpackningsantal 1
Package Length 6.9 in [17.5 cm]
Package Width 5.5 in [14 cm]
Package Height 1.2 in [30 mm]
Fraktvikt (förpackning) 4.9 oz [140 g]

Vad det är i lådan

Ingår i paketet eSATA PCI Express Card
SATA Cable
Low Profile Bracket
Driver CD
Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

