

10/100 Mbps USB Print Server

Product ID: PM1115U



This USB 10/100 Mbps Print Server lets you share one printer between many networked users, instead of having to purchase separate printers for each individual workstation.

The Print server (PM1115U) does not require a dedicated print server PC, so you can position the printer anywhere on your network, while avoiding the performance bottleneck you would experience with an always-on PC acting as the print server.

PM1115U features straightforward installation wizards and remote web-based management, simplifying the print server's installation and use. The palm-sized, lightweight print server plugs directly into your printer's USB port and needs only an RJ-45 networking cable to connect it to the rest of your network.

Compatible with most major operating systems, the 1 Port USB 10/100 Mbps Print Server is the perfect USB printer solution for home or small office networks.

Certifications, Reports and Compatibility

Applications

- Connects your Ethernet network to one USB printer
- PM1115U offers network printing solution for home, small office, educational & government institutions and any other environments that require printer sharing

Features

- Compact and light weight USB print server only weighs 1.6 ounces

- Compliant with USB 2.0
- Configurable using a web based browser or a windows based configuration
- Easy setup and configuration
- Eliminates the need to purchase additional printers for individual workstations
- Share 1 USB printer with computers connected to a home or small office network
- Support SNMP for remote printer management and works with any SNMP based application to access and manage
- Supports 10/100 Mbps fast Ethernet network

Hardware

Warranty	2 Years
Ports	1

Performance

Maximum Data Transfer Rate	100 Mbps
Remote Management Ability	Yes
Supported Protocols	AppleTalk
	IPX
	LPR
	NetBEUI
	SNMP
	TCP/IP

Connector(s)

External Ports	RJ-45
	USB Type-A (4 pin) USB 2.0

Software

OS Compatibility	Windows 8 / 8.1 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000, ME, 98SE
	Windows Server 2012, 2008 R2, 2003(32/64)
	Mac OS 10.x (Tested up to 10.11)



Linux

Special Notes / Requirements

System and Cable Requirements	USB printer cable not included
Note	OS Compatibility refers to the included software only – the Print Server itself can be used without software on any platform that supports network printing

Indicators

LED Indicators	Status
	LAN Connectivity
	Activity

Power

Power Source	AC Adapter Included
Output Voltage	7.5 DC
Output Current	0.5A
Center Tip Polarity	Positive

Physical Characteristics

Color	Beige
Material	Plastic
Product Length	3.0 in [75 mm]
Product Width	2.2 in [55 mm]
Product Height	0.8 in [20 mm]
Weight of Product	1.6 oz [45 g]

Packaging Information

Package Length	9.4 in [24 cm]
Package Width	3.1 in [78 mm]
Package Height	6.2 in [15.8 cm]



Shipping (Package) Weight	18.0 oz [510 g]
------------------------------	-----------------

**What's in the
Box**

Included in Package	Driver CD
	USB Print Server
	Power Adapter (NA)
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

