

1 Port USB Wireless-N 150Mbps AirPrint Server - 802.11b/g/n

Product ID: PM1115UA



The PM1115UA Wireless-N USB AirPrint Server lets you print directly from your iPhone, iPod touch or iPad devices to most standard USB printers over a wireless network. (For a list of compatible printers, see support documentation).

With this compact AirPrint server connected to your existing wireless network, it enables iOS / iPad printing direct from the print menu of your device, without the hassle of transferring your documents or photos to another system.

You can also use the AirPrint server with other laptop and desktop systems on your network, effectively turning any standard USB printer into a fully networked printer. This compact server supports 802.11b/g/n standards and features an easy-to-use web interface as well as print management software for Windows and Mac OS. For added flexibility, up to 2 printers can be connected to the print server using a USB hub (not included).

As an added benefit, using a wireless print server makes your printer available from anywhere within range of your wireless router, so you can place it in a convenient location without being tied down by a network cable.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Print directly from your iOS-based devices over the wireless network
- Convert a standard USB printer into a standalone, wireless printer and share between multiple networked computers
- Place your printer in a convenient, central location without requiring a network cable

Features

- Supports Apple AirPrint on iPad (all models), iPhone (3GS or later) and iPod touch (3rd generation or later)
- Also supports network print sharing with desktop and laptop systems
- Compliant with 802.11b/g/n wireless networks, with data rates up to 150 Mbps
- USB 2.0 support
- Optional 10/100 Mbps RJ45 LAN Port
- Compact footprint
- Easy-to-use web interface and included software for configuration on Windows or Mac OS

Hardware

Warranty	2 Years
Ports	1
Interface	USB 2.0
	RJ45 (10/100 Ethernet)
	Wireless Ethernet
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-T, IEEE 802.11b/g/n Wireless

Performance

Maximum Data Transfer Rate	150 Mbps
Frequency	2.4 GHz
Security Features	WEP Data Encryption
	WPA Data Encryption
	TKIP/AES

		WPA and WPA2-PSK Data Encryption
	Supported Protocols	TCP/IP
<hr/>		
Connector(s)		
	Connector Type(s)	1 - USB 2.0 Type-A (4 pin, 480Mbps)
		1 - RJ-45
		1 - Wireless N (IEEE 802.11n)
<hr/>		
Software		
	OS Compatibility	Windows 11, 10 (32/64), 8 / 8.1 (32/64), 7 (32/64), Vista(32/64), XP(32/64)
		Windows Server 2012, 2008 R2, 2003(32/64)
		Mac OS 10.8 and up (Tested up to 10.9)
<hr/>		
Special Notes / Requirements		
	Note	AirPrint is an Apple technology that is supported on the iPad (all models), iPhone (3GS or later) and iPod touch (3rd generation or later)
		OS Compatibility refers to the included software only – the Print Server itself can be used without software on any platform that supports network printing
		Supports most standard USB printers (For a list of compatible printers, see support documentation)
<hr/>		
Indicators		
	LED Indicators	1 - Power
		1 - WLAN
		1 - LAN
		1 - USB
<hr/>		
Power		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.2 A
	Output Voltage	5 DC

Output Current	1 A
Center Tip Polarity	Positive
Plug Type	M

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	0~70% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	3.3 in [85 mm]
Product Width	2.2 in [5.7 cm]
Product Height	0.9 in [2.4 cm]
Weight of Product	2.0 oz [56 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	5.9 in [15 cm]
Package Height	2.0 in [50 mm]
Shipping (Package) Weight	11.4 oz [324 g]

What's in the Box

Included in Package	1 - Wireless-N USB 2.0 AirPrint Server
	1 - Universal Power Adapter (NA/UK/EU)
	1 - Driver CD
	1 - Instruction Manual

**Warranty
Information**

Warranty

2 Years

****Product appearance and specifications are subject to change without notice.***