

10ft (3m) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Produkt-ID: PXT101_10



This 10 ft Computer Power Cord makes a suitable replacement for worn-out or missing PC and monitor power cables.

Featuring a NEMA 5-15P Plug and a C13 connector, this high quality replacement cable is compatible with most monitors, PCs, scanners and laser printers.

Designed for durability and dependability, this 18 AWG AC power cord is backed by our Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Plugs monitor, PC, laser printer, or scanner into a grounded power outlet

Merkmale

- AC POWER CORD: This 10ft (3m) 18AWG flexible computer power cable with NEMA 5-15P and IEC

60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 10ft (3m) Power Cable | NEMA 5-15P to IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Steckverbinder

Garantiebestimmungen	Lifetime
Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125V (max.)
Eingangsstrom	10A

Physische Eigenschaften

Farbe	Schwarz
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	0.9 in [2.4 cm]
Produkthöhe	0.9 in [2.4 cm]
Produktgewicht	7.6 oz [216.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.4 in [18.7 cm]
Paketbreite	3.0 in [7.7 cm]
Pakethöhe	2.4 in [6.2 cm]
Versandgewicht (Verpackung)	8.3 oz [234.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 10ft Standard Computer Power Cord - NEMA5-15P to C13
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.