

10ft (3m) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Product ID: PXT101_10



This 10 ft Computer Power Cord makes a suitable replacement for worn-out or missing PC and monitor power cables.

Featuring a NEMA 5-15P Plug and a C13 connector, this high quality replacement cable is compatible with most monitors, PCs, scanners and laser printers.

Designed for durability and dependability, this 18 AWG AC power cord is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Plugs monitor, PC, laser printer, or scanner into a grounded power outlet

Features

- **AC POWER CORD:** This 10ft (3m) 18AWG flexible computer power cable with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A.
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817). Fully molded strain relief connectors for durability. 3 Conductor Power Cable made from 100% Copper Wire. Fire Rating: VW-1.

- **SPECS:** 10ft (3m) Power Cable NEMA 5-15P to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SVT Jacket Material: PVC Color: Black Temperature Range: 37F to 140F (3 to 60) Cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Cable Type	SVT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125V (max.)
Input Current	10A

Physical Characteristics

Color	Black
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	0.9 in [2.4 cm]
Product Height	0.9 in [2.4 cm]
Weight of Product	7.6 oz [216.0 g]

Packaging Information

Package Quantity	1
------------------	---

Package Length	7.4 in [18.7 cm]
Package Width	3.0 in [7.7 cm]
Package Height	2.4 in [6.2 cm]
Shipping (Package) Weight	8.3 oz [234.0 g]

What's in the Box

Included in Package	1 - 10 ft Standard Computer Power Cord - NEMA5-15P to C13
---------------------	-----------------------------------------------------------

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***