

3ft (1m) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Product ID: PXT101_3



Our 3ft IBM Power Cable will let you plug a monitor, PC, or laser printer into a grounded power outlet.

This 3ft. power cable is expertly designed and constructed of only top quality materials, and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

Features

- **AC POWER CORD:** This 3ft (1m) 18AWG flexible computer power cable with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A.
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817). Fully molded strain relief connectors for durability. 3 Conductor Power Cable made from 100% Copper Wire. Fire Rating: VW-1.
- **SPECS:** 3ft (1m) Power Cable. NEMA 5-15P to IEC 60320 C13. 18AWG. 125V 10A (Max). Jacket Rating: SVT. Jacket Material: PVC. Color: Black. Temperature Range: 37F to 140F (3 to 60). Cable Outer Diameter: 0.25in (6.3mm).

- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Type	SVT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125V (max.)
Input Current	10A

Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Product Width	1.0 in [2.5 cm]
Product Height	0.9 in [2.4 cm]
Weight of Product	3.5 oz [98.0 g]

Packaging Information

Package Quantity	1
------------------	---

Package Length	2.6 in [6.5 cm]
Package Width	7.8 in [19.9 cm]
Package Height	1.4 in [3.5 cm]
Shipping (Package) Weight	3.5 oz [100.0 g]

**Warranty
Information**

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***