

3ft (1m) Power Extension Cord, C14 to C13, 10A 125V, 18AWG, Computer Power Cord Extension, IEC-320-C14 to IEC-320-C13 AC Power Cable Extension for Power Supply, UL Listed

Product ID: PXT1003



This 3-foot Computer Power Cord Extension Cable can be used as a power cable for your PC, or as an extension cable for your existing computer power cord.

Expertly designed and constructed of high quality materials, the power extension cable (C14 to C13) features one computer power (female) connector and one hooded (male) power connector.

This high quality Power Cord Extension Cable is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend your Monitor, Scanner, Printer, or PC power cord by an additional 3 ft

Features

- **AC POWER CORD:** This 3ft (1m) 18AWG power supply extension cable with IEC 60320 C14 and IEC 60320 C13 connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor extension cord made with 100% copper wire This C14 to C13 power extension cord is

available in other lengths

- **SPECS:** 3ft (1m) AC Power Cord IEC 60320 C14 to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Type: SVT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.24in (6.1mm)

- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 works with North American outlets IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more Replacement PC power supply cable/cord

- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Performance

Warranty	Lifetime
Maximum Cable Length	3.0 ft [0.9 m]

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125V AC
Input Current	10 A

Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Product Width	1.1 in [2.9 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	3.5 oz [98.0 g]

Packaging Information

Package Quantity	1
Package Length	4.8 in [12.1 cm]
Package Width	7.8 in [19.8 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	3.7 oz [104.0 g]

What's in the Box

Included in Package	1 - 3 ft Standard Computer Power Cord Extension - C14 to C13
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*