

6ft (1.8m) Laptop Power Cord, NEMA 5-15P to C5 (Clover Leaf), 10A 125V, 18AWG, Laptop Replacement Cord, Printer Power Cable, Laptop Charger Cord, Laptop Power Brick Cord - UL Listed

Produkt-ID: PXT101NB3S



Our 6 ft. 3-Slot Laptop Power Cord features one NEMA 5-15P and one C5 connector - a suitable replacement notebook power cord or spare power cord for your HP, Toshiba or other compatible laptop. Designed for durability and dependability, the 3-Slot Laptop Power Cord is backed by our Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **AC POWER CORD:** This 6ft (1.8m) 18AWG flexible laptop power cord with NEMA 5-15P and IEC 60320 C5 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief C5 connector for durability | Fire Rating: VW-1 | 3 Conductor Notebook Power Cable made with 100% Copper Wire
- **SPECS:** 6ft (1.8m) Power Cable | NEMA 5-15P to IEC 60320 C5 | 18AWG | 125V 10A (Max) | Jacket

Rating: SJT | Jacket Material: PVC | Color: Black | Temperature Range: 35°F to 140°F (2 to 60) | Cable Outer Diameter: 0.3in (7.62mm)

- **COMPATIBILITY:** AC Power Cord NEMA 5-15P works with North American outlets | IEC C5 connector works with most power bricks for laptops/notebooks, monitors, scanners, printers, and more | Replacement laptop power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this laptop charger cord is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
----------------------	----------

Anzahl von Leitern	3
--------------------	---

Kabeltyp	SJT
----------	-----

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
------------------	-----------------------------------

Steckverbinder B	1 - IEC 60320 C5 Strom
------------------	------------------------

Spezielle Hinweise/Anforderungen

Hinweis	UL gelistet
---------	-------------

Strom

Eingangsstrom	10A
---------------	-----

Physische Eigenschaften

Farbe	Schwarz
-------	---------

Drahtstärke	18 AWG
-------------	--------

Kabellänge	6.0 ft [1.8 m]
------------	----------------

Produktlänge	6.0 ft [1.8 m]
--------------	----------------

Produktbreite	0.9 in [2.4 cm]
---------------	-----------------

Produkthöhe	0.9 in [2.3 cm]
-------------	-----------------

Produktgewicht	6.7 oz [189.0 g]
----------------	------------------

Verpackungsinformationen

Paketmenge	1
Paketlänge	4.1 in [10.3 cm]
Paketbreite	7.9 in [20.0 cm]
Pakethöhe	1.4 in [3.6 cm]
Versandgewicht (Verpackung)	7.2 oz [204.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 1,8 m Standard Laptop Stromkabel - NEMA 5-15P auf C5
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.