

10ft (3m) Laptop Power Cord, NEMA 1-15P to C7, 7A 125V, 18AWG, Laptop Replacement Cord, Printer Power Cable, Laptop Charger Cord, Laptop Power Brick Cord
- UL Listed

Produkt-ID: PXT101NB10



This PXT101NB10 high quality 10-foot Laptop Power Cord offers a durable power connection for notebook computers, backed by lifetime warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Spare / replacement cable for your laptop
- Laptop accessory for mobile professionals

Merkmale

- **AC POWER CORD:** This 10ft (3m) 18AWG flexible laptop power cord with NEMA 1-15P and IEC 60320 C7 connectors is suitable for workstation/home office use | Rated to carry 125V at 7A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | Fire Rating: VW-1 | 2 Conductor Notebook Power Cable made with 100% Copper Wire

- **SPECS:** 10ft (3m) Power Cable | NEMA 1-15P to IEC 60320 C7 | 18AWG | 125V 7A (Max) | Jacket Rating: SPT-2 | Jacket Material: PVC | Color: Black | Temperature Range: 35°F to 140°F (2 to 60) | Cable Outer Diameter: 0.3in (7.62mm)
- **COMPATIBILITY:** AC Power Cord NEMA 1-15P works with North American outlets | IEC C7 connector works with most power bricks for laptops/notebooks, monitors, scanners, printers, and more | Replacement laptop power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this laptop charger cord is backed for life, including free lifetime 24/5 multilingual technical assistance

Leistung

Garantiebestimmungen Lifetime

Max. Kabellänge 10.0 ft [3.0 m]

Steckverbinder

Steckverbinder A 1 - NEMA 1-15 Strom (Nordamerika)

Steckverbinder B 1 - IEC 60320 C7 Strom (unpolarisiert)

Spezielle Hinweise/Anforderungen

Hinweis UL Listed

Strom

Eingangsspannung 125 AC

Eingangsstrom 7A

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 18 AWG

Kabellänge 10.0 ft [3.0 m]

Produktlänge 10.0 ft [3.0 m]

Produktbreite 1.0 in [2.5 cm]

Produkthöhe 0.8 in [2.0 cm]

Produktgewicht		5.1 oz [144.0 g]
Verpackungsinformationen		
Paketmenge		1
Paketlänge		3.1 in [7.9 cm]
Paketbreite		8.8 in [22.4 cm]
Pakethöhe		1.1 in [2.8 cm]
Versandgewicht (Verpackung)		5.5 oz [156.0 g]
Verpackungsinhalt		
Im Paket enthalten		1 - 10ft Standard Laptop Power Cord - NEMA 1-15P to C7
Garantieinformationen		
Warranty		Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.