

10ft (3m) Heavy Duty Power Cord, NEMA 5-15P to C19 AC Power Cord, 15A 125V, 14AWG, Computer Power Cord, Heavy Gauge Power Cable for PDUs and Network Equipment, NEMA 5-15P to IEC 60320 C19 Power Cord

Produkt-ID: PXT515191410



This NEMA 5-15P-to-C19 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for high-end server equipment such as routers, switches, Power Distribution Units (PDU), etc.

Plus, you can use the cable to extend the reach of your existing power cord by 10 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXT515191410 power cord is backed by a lifetime warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connect your high-power server equipment to a power outlet
- Extend your existing power cord by 10 feet

Merkmale

- **HEAVY DUTY AC POWER CORD:** This 10ft (3m) 14AWG universal power cord with NEMA 5-15P and IEC 60320 C19 connectors is suitable for workstations/home office use | Rated to carry 125V at 15A
- 2,5 mm²-Kabel
- UL, RoHS-konform
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets | IEC C19 connector works with most servers and networking equipment | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SJT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C19 Strom

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	15 A

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	14 AWG

Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktgewicht	17.3 oz [490 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	9.7 in [24.6 cm]
Paketbreite	3.9 in [10.0 cm]
Pakethöhe	2.8 in [7.2 cm]
Versandgewicht (Verpackung)	1.1 lb [0.5 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 10 ft 14 AWG Computer Power Cord - NEMA 5-15P to IEC 320 C19
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.