

6ft (1.8m) Heavy Duty Power Cord, NEMA 5-15P to C19 AC Power Cord, 15A 125V, 14AWG, Computer Power Cord, Heavy Gauge Power Cable for PDUs and Network Equipment, NEMA 5-15P to IEC 60320 C19 Power Cord

Produkt-ID: PXT515C19146



This NEMA 5-15P-to-C19 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for high-end server equipment such as routers, switches, Power Distribution Units (PDU), etc.

Plus, you can use the cable to extend the reach of your existing power cord by 6 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXT515C19146 power cord is backed by a lifetime warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connect your high-power server equipment to a power outlet
- Extend your existing power cord by 6 feet

Merkmale

- **HEAVY DUTY AC POWER CORD:** This 6ft (1.8m) 14AWG universal power cord with NEMA 5-15P and IEC 60320 C19 connectors is suitable for workstations/home office use | Rated to carry 125V at 15A
- 2,5 mm²-Kabel
- UL, RoHS-konform
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets | IEC C19 connector works with most servers and networking equipment | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SJT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C19 Strom

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	15 A

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	14 AWG

Kabellänge	6.0 ft [1.8 m]
Produktlänge	6.0 ft [1.8 m]
Produktgewicht	11.6 oz [328 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	8.0 in [20.4 cm]
Paketbreite	3.2 in [8.2 cm]
Pakethöhe	2.6 in [6.6 cm]
Versandgewicht (Verpackung)	11.8 oz [334.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 6 ft 14 AWG Computer Power Cord - NEMA 5-15P to IEC 320 C19
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.