

3ft (1m) Heavy Duty Extension Cord, IEC 320 C13 to IEC 320 C20 Black Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, IEC 320 C13 to IEC 320 C20 AC Power Cord - UL Listed

Product ID: PXTC13C20143



This C13 to C20 power cord from StarTech.com features 14 AWG wire that's suitable for high-power connections, making it perfect for server application and connecting to a Power Distribution Unit (PDU).

Expertly designed and constructed of high-quality materials, the PXTC13C20143 power cord is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 3 feet

Features

- **HEAVY DUTY EXTENSION CORD:** This 3ft (1m) 14AWG universal power cord with IEC 60320 C13 to IEC 60320 C20 connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability

Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths

• SPECS: 3ft (1m) AC Power Cord IEC 60320 C13 to IEC 60320 C20 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: -4 to 140F (-20 to 60C) Cable Outer Diameter: 0.36in (9.14mm)

• COMPATIBILITY: PC Power Cord C13 works with most computer hardware Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord

• THE IT PRO'S CHOICE: Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C13 Power
Connector B	1 - IEC 60320 C20 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Weight of Product	8.0 oz [228 g]

Packaging Information

Package Quantity	1
Package Length	10.2 in [25.8 cm]
Package Width	5.7 in [14.4 cm]
Package Height	2.0 in [5.1 cm]
Shipping (Package) Weight	6.6 oz [186.0 g]

What's in the Box

Included in Package	1 - 3 ft 14 AWG Computer Power Cord - C13 to C20
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***