

3ft (1m) USB C Charging Cable, Coiled Heavy Duty Fast Charge & Sync USB-C Cable, USB 2.0 Type-C Cable, Rugged Aramid Fiber, Durable Male to Male USB Cable, Black

**Product ID:** R2CCC-1M-USB-CABLE



This 3.3ft (1m) coiled USB C cable can withstand the daily demands of charging and syncing your mobile devices. It contracts to 1.2ft (38cm) making it compact and convenient to store.

The durable USB C charging cable has aramid fiber reinforcement that shelters it from the stress of frequent bends. This also lets the cable flex without over-stretching or damaging the core of the cable.

The USB C cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 5,000+ bend cycles at a 180 angle.

The durable cable supports all USB 2.0 specifications providing a dependable connection for all your USB-C devices. It supports up to 3A for charging your USB C compatible devices.

R2CCC-1M-USB-CABLE is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

## Features

- USB C CHARGING CABLE: Coiling cable stretches up to 3.3ft (1m) and contracts to 1.2ft (38cm) preventing it from

being tangled; Strong but soft flexible TPE jacket, makes it easy to coil and put away in vehicle console or glove compartment

- **RUGGED DESIGN:** USB Type-C cable reinforced with aramid fiber for increased tensile strength; Tested to withstand 10000+ insertions & 5000+ bend cycles at 180 angle; Durable TPE jacket and strain relief; TPE is non-toxic, halogen free
- **FAST CHARGE AND SYNC :** Supporting up to 3A for fast charging from a USB-C port or Quick Charge power adapter, this high quality cord is designed to charge and sync your USB C devices
- **USB-C COMPATIBILITY:** Heavy duty data transfer cable allows you to charge and sync your USB Type C devices including iPad Pro, Samsung Galaxy, One Plus, Google Pixel; (\*Please note that USB 2.0 cables do not support video)
- **SPECS:** Length: 3ft (1m) Color: Black Connectors: USB-C to USB-C Performance: USB 2.0 Material: Aramid Fiber Power: 3A Jacket Type: TPE Shielding: EMI Protection

#### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | Lifetime                       |
| Connector Plating     | Nickel                         |
| Cable Jacket Material | TPE - Thermoplastic Elastomers |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

#### Performance

|                      |                      |
|----------------------|----------------------|
| Maximum Cable Length | 39.4 in [1000 mm]    |
| Type and Rate        | USB 2.0 - 480 Mbit/s |

#### Connector(s)

|             |   |
|-------------|---|
| Connector A | 1 - USB Type-C (24-pin) USB 2.0 (480Mbps) |
|             | 1 - USB Type-C (24-pin) USB 2.0 (480Mbps) |

#### Environmental

|                       |                       |
|-----------------------|-----------------------|
| Operating Temperature | 0 to 80C (32 to 176F) |
| Storage Temperature   | 0 to 80C (32 to 176F) |
| Humidity              | 0% to 95% RH          |

#### Physical Characteristics

|                 |          |
|-----------------|----------|
| Color           | Black    |
| Connector Style | Straight |

|                   |                   |
|-------------------|-------------------|
| Wire Gauge        | 22/32 AWG         |
| Cable Length      | 3.3 ft [1 m]      |
| Cable OD          | 0.1 in [3.1 mm]   |
| Product Length    | 15.1 in [38.3 cm] |
| Product Width     | 0.5 in [1.2 cm]   |
| Product Height    | 0.2 in [0.6 cm]   |
| Weight of Product | 1.5 oz [42.0 g]   |

---

#### Packaging Information

|                           |                  |
|---------------------------|------------------|
| Package Quantity          | 1                |
| Package Length            | 4.9 in [12.5 cm] |
| Package Width             | 8.7 in [22.0 cm] |
| Package Height            | 0.6 in [1.4 cm]  |
| Shipping (Package) Weight | 1.7 oz [48.0 g]  |

---

#### What's in the Box

|                     |  |
|---------------------|--|
| Included in Package | 1 - Rugged USB-C to USB-C Coiled Cable |
|---------------------|--|

---

***\*Product appearance and specifications are subject to change without notice.***