

Wi-Fi travel router for iPad and mobile devices

Produkt ID: R150WN1X1T

This Wireless N travel router lets you create a portable wireless hot-spot from a wired network connection or an existing wireless network, to share with all of your Wi-Fi® enabled devices, including tablets, laptops, Ultrabooks™, or smartphones.

Support for several operating modes helps you create, share or extend a wireless connection while traveling between hotel rooms, conference centers, or boardrooms. The travel Wi-Fi router offers a pocket-sized, USB-powered design with support for Wireless N data rates (backward compatible with 802.11b/g networks).

Directly configurable using any wireless device with a web browser, the travel router supports several additional operation modes including WISP (Wireless Internet Service Provider - AP & Client), which lets you share an existing WiFi connection with multiple devices, or WiFi repeater mode, which extends the coverage area of an existing wireless network to avoid dead spots.

The USB-powered wireless router is designed to fit directly over your iPad wall charger. For other USB wall chargers or an available USB port on a laptop, we've included a USB extension cable to power the device. The portable router also offers a front port for USB charging, allowing you to charge your devices as needed.

R150WN1X1T is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Extend the coverage area or increase the signal strength in "dead spots" of an existing Wireless-N signal
- Create a wireless access point for tablets, laptops and smartphones in a hotel room with only wired connections
- Share one paid wireless connection with multiple devices using WISP mode
- Add a wireless hotspot in a boardroom or conference center to share with your co-workers

Funktioner

- Supports several operating modes including: WiFi Access Point (AP), WISP (AP & Client) and WiFi Repeater functions
- Backward compatible with IEEE 802.11g, and 802.11b WiFi networks
- Supports WEP, WPA and WPA2 wireless authentication

- Built-in configuration utility (web-based)
- Integrated front USB charge port
- Compliant with IEEE 802.11n (Wireless-N), with speeds up to 150 Mbps
- Compact design fits over your iPad® power adapter
- Included USB extension cable for powering with other laptop or tablet USB wall chargers and ports

Hårdvara

Garantipolicy	2 Years
Portar	1
Gränssnitt	Trådlöst Ethernet
Antennkonfiguration	1x1:1 (TxR:S)
Industristandarder	IEEE 802.11b, IEEE 802.11g, IEEE 802.11n, IEEE 802.3, IEEE 802.3u

Prestanda

Maximal dataöverföringshastighet	150 Mbps
Maximalt avstånd	10 m / 33 ft
Kompatibla nätverk	10/100 Mbps
Frekvensområde	2.4 ~ 2.4835 GHz
Modulering	DSSS (BPSK/QPSK/CCK), OFDM (BPSK/QPSK/16QAM/64QAM)
Säkerhetsfunktioner	WEP-datakryptering WPA-datakryptering
Allmänna specifikationer	Maximum Clients: 5

Kontakt(er)

Kontakttyp(er)	Trådlös N (IEEE 802.11n)
Interna portar	USB Type-A (4-stifts) USB 2.0



Externa portar USB Type-A (4-stifts) USB 2.0

RJ-45

Särskilda
anmärkningar/
krav

System- och
kabelkrav

iPad charger, or other USB power adapter / charge port

Wired network connection

Indikatorer

LED-indikatorer

Power / WiFi Status

Ström

Power Source

Strömförsörjd via USB

Miljö

Drifttemperatur

0°C to 55°C (32°F to 131°F)

Förvaringstemperatur

-20°C to 55°C (-4°F to 131°F)

Luftfuktighet

0~90% RH (Non-Condensing)

Utseende

Färg

Vit

Kabinettyp

Av plast

Produktlängd

1.9 in [47.0 mm]

Produktbredd

2.2 in [55.0 mm]

Produkt höjd

1.4 in [35.0 mm]

Produktvikt

4.2 oz [120.0 g]

Förpackning

Package Length

6.5 in [16.5 cm]

Package Width

4.3 in [11.0 cm]

Package Height

1.6 in [40.0 mm]



Fraktvikt
(förpackning) 11.8 oz [335.0 g]

Vad det är i
lådan

Ingår i paketet	Travel Router
	USB Extension Cable
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

