

Cat5e Patch Cable with Snagless RJ45 Connectors - 4 ft, Blue

ID prodotto: RJ45PATCH4



This 4-foot Cat5e cable meets or exceeds all Category 5e cable specifications to ensure reliable Ethernet network connections. Plus, the cable features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

For easier cable runs, the snagless connectors protect the cable's RJ45 clips during installation, making them less likely to snag or break. This ensures a sturdy connection by preventing the cable from becoming loose from the port.

The cable features moulded boots that offer connector strain relief, by stopping the RJ45 connector termination points from bending at sharp angles, and reducing the risk of damage to the cable, which could decrease network performance.

Get the highest value for your cable investment with our Cat 5e cables, each one manufactured using high-quality copper conductors.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The RJ45PATCH4 is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certificazioni, report e compatibilità



Applicazioni

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Caratteristiche

- RJ45 connector clip protectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Molded strain relief prevents the cable from being bent at sharp angles at the RJ45 connector, to minimize the stress at the plug termination point
- Constructed with top quality components
- High quality 24 AWG copper wire

Hardware

Norme di garanzia	Lifetime
Numero di conduttori	4 Pair UTP
Tipo guaina cavo	PVC - Polyvinyl Chloride
Classe di resistenza al fuoco	Classe CM
Tipo cavo	Antigroviglio

Prestazioni

Classe cavo	CAT5e - 100 MHz
-------------	-----------------

Connettore/i

Connettore A	1 - RJ-45
--------------	-----------

Connettore B		1 - RJ-45
Caratteristiche fisiche		
	Colore	Blu
	Diametro filo	24 AWG
	Lunghezza del cavo	4.0 ft [1.2 m]
	Lunghezza prodotto	4.0 ft [1.2 m]
	Larghezza prodotto	0.5 in [1.2 cm]
	Altezza prodotto	0.5 in [1.4 cm]
	Peso prodotto	1.7 oz [47.0 g]
Informazioni confezione		
	Quantità confezione	1
	Lunghezza Confezione	6.9 in [17.6 cm]
	Larghezza del Pacco	6.1 in [15.4 cm]
	Altezza del Pacco	1.1 in [2.8 cm]
	Peso spedizione (confezione)	2.3 oz [64.0 g]
Contenuto della confezione		
	Incluso nella confezione	1 - 4 ft. Cat5e Patch Cable - Blue
Informazioni sulla garanzia		
	Warranty	A vita

* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.