

## Refurbished 12U 19in Wall Mount Server Rack Cabinet w/ Steel Mesh Door

**Product ID:** RK1219WALLMR



This refurbished 12U 19in Wall Mounted Server Rack Cabinet is perfect for safely mounting routers, switches, media converters, and other networking equipment. Features a sturdy steel design and a vented tempered glass door to keep your equipment safe and cool.

Suited for server rooms, wiring closets, manufacturing areas, warehouses, or anywhere where networking equipment needs to be protected.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

## Certifications, Reports and Compatibility



## Applications

- Audio/Visual control centers
- Data centers
- Industrial control centers
- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Telecommunication closets

## Features

- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Steel mesh door for added security

---

### Hardware

Warranty	None
Wallmountable	Yes
Rack Type	4-Post
Frame Type	Steel
U Height	12U
Special Features	Ships Fully Assembled
	Wall-Mountable
Fan Options	Two Optional Fans: 120 mm
Industry Standards	EIA RS310-C

---

### Performance

Weight Capacity	132.3 lb [60 kg]
-----------------	------------------

---

### Physical Characteristics

Color	Black
Front Door Construction	Steel Mesh
Front Door Features	Secure Key Lock
Side Panel Construction	Steel

---

### Product Measurements

Internal Depth	22.5 in [57.2 cm]
Product Length	21.7 in [55.0 cm]
Product Width	23.5 in [59.7 cm]
Product Height	25.0 in [63.5 cm]
Weight of Product	55.4 lb [25.1 kg]
Maximum Mounting Depth	16.2 in [41.3 cm]

---

#### Packaging Information

Flat Pack (Assembly Required)	No
Package Length	27.6 in [70.0 cm]
Package Width	26.2 in [66.5 cm]
Package Height	26.1 in [66.2 cm]
Shipping (Package) Weight	62.0 lb [28.1 kg]

---

#### What's in the Box

Included in Package	1 - 19in Cabinet
	1 - Package of Cab screws and Cage Nuts
	1 - Keys

---

#### Warranty Information

Warranty	Refurbished 90 Days
----------	---------------------

---

***\*Product appearance and specifications are subject to change without notice.***