


8U Desktop Rack - 2-Post Open Frame Rack

Product ID: RK8OD



This 2-post desktop rack provides 8U of storage space for mounting smaller A/V and IT equipment.

With this 2-post rack, you can mount equipment at a fraction of the cost of conventional racks. The lightweight rack is engineered to meet EIA-310 rack-mount standards and is constructed of solid steel, ensuring a sturdy and safe mounting solution for your mission-critical equipment.

The rack features an open frame, free standing design that saves space with a small footprint. It gives you the ability to place rack-mount equipment on any surface in your office, such as your desk. This makes it easy to access your equipment on a daily basis.

The 2-post rack is easy to assemble and includes a pack of 20 M5 screws and cage nuts.

If you're looking for a desktop mounting solution with more rack units, StarTech.com also offers a [%product id="RK12OD" text="12U 2-post desktop rack"%].

The RK8OD is backed by a StarTech.com lifetime warranty and free technical support.

Certifications, Reports and Compatibility



Applications

- Place KVMs and rack-mount computers or server systems neatly on or beside your desk
- Save space in your SoHo (small office, home office) or server room, by placing equipment on desk or other surface, instead of taking up floor space

Features

- Save money with a rack-mount solution that's a fraction of the cost of conventional racks
- Improve efficiency in your office or server room by placing equipment on your desk
- Easy setup with hassle-free assembly and mounting hardware included
- Includes 20 M5 screws and cage nuts
- Lightweight design
- EIA-310 compliant

Hardware	Warranty	Lifetime
	Wallmountable	No
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	8U
	Special Features	U-Markings
	Special Features	Easy Assembly
	Mounting Rail Profile	G-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance	Weight Capacity	110.5 lb [50 kg]
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Product Length	11.5 in [2.9 cm]
	Product Width	19.8 in [5.0 cm]
	Product Height	16.1 in [4.1 cm]
	Weight of Product	4.8 lb [2.2 kg]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Package Length	21.7 in [5.5 cm]
	Package Width	4.4 in [1.1 cm]
	Package Height	3.2 in [81 mm]
	Shipping (Package) Weight	5.8 lb [2.6 kg]

What's in the Box	Included in Package	Left Base Bracket
	Included in Package	Right Base Bracket
	Included in Package	Left Vertical Rail
	Included in Package	Right Vertical Rail
	Included in Package	Front Base Bracket
	Included in Package	Rubber Feet
	Included in Package	Assembly Screws
	Included in Package	M5 Screws
	Included in Package	M5 Cage Nuts
	Included in Package	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

