

2U Rack Mount Security Cover - Hinged Locking Rack Panel/ Cage/Door for Physical Security/ Access Control of 19" Server Rack & Network Cabinet - Assembled w/Mounting Hardware

Product ID: RKSECLK2U



Prevent unauthorized access to your servers and networking equipment with this Server Cabinet Security Cover. The front panel is perforated for airflow, while not compromising on security. The hinged 2U security panel is suitable for floor standing server racks or wall-mount racks. The server rack security door is excellent for retail, classrooms, medical offices or anywhere partial access needs to be secured.

The hinged 2U security panel lets you quickly open the door, make your required adjustments, and simply close the security rack panel to restore the professional appearance of your server room. The rack security cover also comes complete with rack installation screws and nuts, providing everything needed to ensure a hassle-free installation. The screws mounting the RKSECLK2U to your server rack are housed behind its locking hinged panel. This feature increases security however it only allows for 1U of equipment to be accessed.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

This RKSECLK2U is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Easily access the inside of your rack, with a hinged design
- Excellent for retail, classrooms, medical offices or anywhere partial access needs to be secured

Features

- **PREVENT UNAUTHORIZED ACCESS:** This 2U 19" hinged rack mount security cover is designed to cover 1U of network equipment or servers while maintaining convenient quick access via lock and key
- **VENTED AIRFLOW:** This server rack panel with a vented front is designed to facilitate airflow & provide visual access to equipment
- **STURDY CONSTRUCTION:** The server rack cage is a robust EIA-310 compliant solution made with SPCC commercial cold-rolled steel and provides physical security and controlled access to your equipment
- **EASY TO INSTALL:** This fully assembled server cabinet door can be installed without removing or powering down the protected equipment already in place and includes mounting hardware as well as 2 keys
- **3 YEAR WARRANTY:** StarTech.com offers 24 hour technical support and has been the choice of IT professionals for 30 years, conducting thorough compatibility and performance testing on all our products

Hardware

Warranty	3 Years
U Height	2U *1U available for equipment*
Front Door Construction	Steel
Front Door Features	Secure Key Lock

Physical Characteristics

Color	Black
Construction Material	Steel
Material	Steel
Product Length	19.4 in [49.3 cm]
Product Width	2.6 in [65.0 mm]
Product Height	3.3 in [85.0 mm]
Weight of Product	4.0 lb [1.8 kg]

Packaging Information

Package Length	21.3 in [54.0 cm]
Package Width	5.9 in [15.0 cm]
Package Height	4.2 in [10.6 cm]



Shipping (Package) Weight	4.8 lb [2.2 kg]
------------------------------	-----------------

What's in the Box

Included in Package	Hinged Security Lock Panel
	M5 Screws
	M5 Cage Nuts
	Keys

****Product appearance and specifications are subject to change without notice.***

