


## Universal Swivel VESA LCD Mounting Bracket for 19in Rack or Cabinet

Produkt ID: RKLCDDBKT



The RKLCDDBKT Universal Swivel VESA LCD Mounting Bracket for 19in Rack or Cabinet lets you mount almost any retail LCD or touch screen into a server rack/cabinet, with tilt and swivel motion for maximum visible range. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Hinged on one of the rail mounts, the LCD bracket can be released to swing out from the rack, as well as offering vertical tilt allowing for perfect placement of your LCD panel with minimal adjustment.

Constructed from solid cold pressed steel (SPCC), the LCD mounting bracket is designed to support 75mm and 100mm VESA mounted panels, and meets ANSI/EIA RS-310-D rack mounting standards.

Backed by a StarTech.com Lifetime warranty.

## Certifikat, rapporter och kompatibilitet

### Användning

- Ideal for installing a retail LCD monitor into an existing Rack or Cabinet
- Installing a touch screen display into a rack or cabinet while retaining access behind it with the swing it out arm
- Can be mounted at any height in the rack; with swivel bracket the screen is always visible

### Funktioner

- 100mm and 75mm VESA mounting hole pattern
- Meets ANSI/EIA RS-310-D standards
- TAA compliant for GSA Schedule purchases
- Constructed from solid steel at 2.0mm thick, this bracket is designed for durability

---

#### Hårdvara

Garantipolicy	Lifetime
Ramtyp	Stål
U-höjd	7U
Kabelhantering	Nej
Industristandarder	EIA RS310-D

---

#### Prestanda

Weight Capacity (Stationary)	35.4 lb [16 kg]
Allmänna specifikationer	VESA Compliance: 100x100mm 75x75mm

---

#### Utseende

Färg	Svart
Kabinettyp	Stål
Inre bredd	16.7 in [42.5 cm]
Produktvikt	6.3 lb [2.9 kg]

---

#### Förpackning

Package Length	19.3 in [48.9 cm]
Package Width	12.7 in [32.3 cm]
Package Height	4.2 in [10.6 cm]
Fraktvikt (förpackning)	7.0 lb [3.2 kg]



---

Vad det är i  
lådan

Ingår i paketet

Mounting back plate

LCD Swivel Mounting Bracket

Package of assembly screws (4 x M5\*16 Panel screws, 4 x M5  
Cage nuts, 2 x M4\*8 screws)

Package of 4 LCD mounting Screws

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

