

4U Blank Panel for 19 inch Rack - Rack Mount Blanking Panel for Server/Network Racks, Enclosures & Cabinets - 4RU Rack Filler Panel/Spacer/Plates - Solid Panel - Steel

Product ID: RKP4U



This 4U blanking panel helps improve the appearance and airflow of your EIA-310 compliant 19 in. server rack.

This solid blank rack panel creates a clean and professional look by covering empty rack spaces and visible cables, for a more organized server room.

When used to cover unused rack units, this 4RU panel can help to control airflow and in certain applications, control internal temperatures by reducing the recirculation of hot air within the rack, created when unused spaces are left uncovered.

RKP4U is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

Features

- **COMPATIBLE WITH 19" WIDE RACKS:** This 4U blank panel is designed to EIA-310 specifications and fits all 19" standard network/server racks and cabinets; ships with hardware to mount this metal panel to your rack, installation is quick and easy

- **PROTECT YOUR EQUIPMENT:** This solid blanking panel/spacer helps to protect valuable rackmount server equipment by creating space between installed devices, promoting airflow and passive cooling
- **TECHNICAL SPECIFICATIONS:** Width: 19 inches Height: 4U (7 in.) Color: Black Power Coated Finish Solid (non-vented) Includes 2 Sets of M6 Cagenuts and Screws Cold-Rolled Steel
- **BUILT TO LAST:** Blanking panels/plates are made with 1.2mm thick cold-rolled steel; this filler panel is designed to hold up to be durable while managing airflow around your networking equipment
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; This 4U rackmount blanking panel is backed for life by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	2 Years
U Height	4U
Industry Standards	EIA-310-D

Physical Characteristics

Color	Black
Material	Steel
Product Length	19.0 in [48.2 cm]
Product Width	7.0 in [17.7 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	2.3 lb [1.0 kg]

Packaging Information

Package Quantity	1
Package Length	20.7 in [52.6 cm]
Package Width	7.6 in [19.2 cm]
Package Height	1.1 in [2.8 cm]
Shipping (Package) Weight	2.7 lb [1.2 kg]

What's in the Box

Included in Package	1 - 4U Blank Panel
---------------------	--------------------

4 - M6 Screws

4 - M6 Cage Nuts

****Product appearance and specifications are subject to change without notice.***