

3.3ft (1m) Rugged USB Multi Charging Cable, USB to Lightning/Micro-USB/Type-C, Apple MFi Certified, Aramid Jacket, Universal 3-in-1 USB Charger Cord for iPhone/iPad/Android

**Product ID:** RLTCUB1MBK



This USB Multi Charging Cable is a single-cable solution to conveniently charge your Apple Lightning, USB-C, or Micro-USB devices

Keep this USB to Micro-USB, USB-C or Lightning cable on hand and minimize the need for carrying multiple charging cables. The 3-in-1 charger cord makes it easy to switch between different portable devices. The cable can charge one device at a time.

Charge your devices from a USB wall charger, car charger, or power bank. The attached connectors are quickly interchangeable for compatibility across multiple USB devices.

The cable's rugged design ensures optimal protection against wear from frequent daily use. The flexible TPE jacket absorbs stress from repeated bends, and Aramid-reinforced construction enhances tensile strength for long-term durability.

To charge or sync a USB-C or Lightning mobile device, simply attach the corresponding connector to the Micro-USB connector and plug into your device. To charge or sync a Micro-USB device, plug just the middle connector of the cable into your mobile device.

RLTCUB1MBK is Apple MFi certified for guaranteed compatibility with Apple Lightning-enabled devices.

## Certifications, Reports and Compatibility



## Applications

- Rugged cable construction enhances durability for long-term use
- Reduce cable clutter and the need for carrying multiple charging cables
- Intuitive connector design is simple to use for quick and seamless interchangeability

## Features

- **3-IN-1 CHARGING CABLE:** Simplify USB charging using this single cable which is compatible with various USB-C, Micro-USB and Apple devices; Note: This cable can only charge one device at a time
- **DURABLE CONSTRUCTION:** Rugged cable design is ideal for frequent daily use; Reinforced w/Aramid fiber for optimal tensile strength; Flexible TPE jacket absorbs bending stress and protects from wear; Tested to withstand 30,000+ bend cycles at +/-90deg
- **APPLE MFI CERTIFIED:** Apple MFi Certified cable for guaranteed compatibility and consistent power output to iPhone and iPad devices with Lightning ports
- **APPLICATIONS:** 3-in-1 charger cord reduces clutter and is ideal for travelling and on-the-go charging; Compatible with USB wall chargers/docks/hubs/power banks; Supports 480Mbps file transfer for syncing portable devices
- **SPECS:** Black; 3.3-foot (1-meter); USB-A to Micro-USB/USB-C/Lightning; Apple MFi Certified; Up to 15W 3A; USB 480Mbps (USB 2.0); TPE Jacket w/Al-Mylar Shield; Nickel-Plated Connectors; Cable O.D.: 5.6mm (0.18in)

---

### Hardware

Warranty	2 Years
Active or Passive Adapter	Passive
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid
Cable Type	Passive Copper Cable

---

### Performance

Maximum Data Transfer Rate	480Mbps
----------------------------	---------

---

### Connector(s)

Connector A	1 - USB 2.0 Type-A
Connector B	1 - 5 pin Micro-USB B Male
	1 - Apple Lightning Connector (8-pin)

1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

---

**Environmental**

Operating Temperature	0&degC to 60&degC (32&degF to 140&degF)
Storage Temperature	-20&degC to 60&degC (-4&degF to 140&degF)
Humidity	40-65%

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.4 in [8.9 mm]
Product Height	0.6 in [1.6 cm]
Weight of Product	1.4 oz [41.0 g]

---

**Packaging Information**

Package Length	7.0 in [17.7 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.6 in [1.4 cm]
Shipping (Package) Weight	1.6 oz [44.0 g]

---

**What's in the Box**

Included in Package	1 - 3-in-1 USB Charge Cable
---------------------	-----------------------------

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*