

## 12U Rack Enclosure Server Cabinet - 21 in. Deep - Wood Finish - Flat Pack

Product ID: RKWOODCAB12



The RKWOODCAB12 12U Office Server Cabinet lets you store your server, network or AV equipment discreetly in the office, with a stylish wood finish. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Designed to blend in with your office or boardroom furniture, this 12U server cabinet features wood laminate exterior panels with a shaded glass front window that keeps your equipment visible for monitoring, as well as front and rear key-locks to prevent unauthorized access. To help keep your valuable equipment running cooler, we've included a ventilation panel to maximize airflow. The cabinet also features durable casters, so that positioning your server equipment as needed isn't a hassle.

The 4-post enclosed rack supports a weight capacity of up to 300lbs (136kg) and offers rails with adjustable mounting depth from 17in (423mm) to 21in (523mm) to accommodate various sizes of equipment. Making it easy to route your cables where you need them, the 12U cabinet offers cable grommets on the rear and top panels, and a cable entry panel at the base.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Mount server or networking equipment in a well-furnished boardroom
- Add an attractive server cabinet that won't be an eyesore in small / home-office areas with limited space

### Features

- 12U Enclosed cabinet with a stylish wood finish
- Supports a weight capacity of up to 300lbs (136kg)
- Adjustable mounting depth from 16.7in (423mm) to 20.6in (523mm)
- Casters included
- Front and rear key-lock
- Flat-packed for easy shipping
- Ventilation and cable entry panels
- TAA compliant for GSA Schedule purchases

<b>Hardware</b>	Warranty	2 Years
	Wallmountable	No
	Rack Type	4-Post
	Frame Type	Aluminum
	U Height	12U
	Special Features	Adjustable Mounting Rails
	Special Features	Leveling Feet
	Special Features	Easy Assembly
	Special Features	Casters (Included)
	Mounting Rail Profile	L-Shape
	Fan Options	Two Optional Fans: 92 mm
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
<b>Performance</b>	Weight Capacity (Stationary)	300.7 lb [136.1 kg]
<b>Physical Characteristics</b>	Color	Black & Brown
	Front Door Construction	Steel with Glass/Acrylic Window
	Front Door Features	Secure Key Lock with Reversible and Removable Front Door
	Side Panel Construction	Wood
	Rear Door Construction	Wood
	Rear Door Features	Secure Key Lock with Removable Back Door
<b>Product Measurements</b>	Internal Width	20.5 in [5.2 cm]
	Internal Depth	25.1 in [6.4 cm]
	Product Length	26.0 in [6.6 cm]

Product Width	22.0 in [5.6 cm]
Product Height	25.6 in [6.5 cm]
Weight of Product	67.8 lb [30.7 kg]
Maximum Mounting Depth	20.6 in [5.2 cm]
Minimum Mounting Depth	16.6 in [4.2 cm]
Product Height with Casters	28.4 in [7.2 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	Yes
Package Length	29.6 in [7.5 cm]
Package Width	29.6 in [7.5 cm]
Package Height	1.8 in [46 mm]
Shipping (Package) Weight	76.7 lb [34.7 kg]

---

**What's in the Box**

Included in Package	Left Side Panel
Included in Package	Ventilation Panel
Included in Package	Cable Entry Panel
Included in Package	Right Side Panel
Included in Package	Rack Rails
Included in Package	Panel Brackets
Included in Package	Rack Bottom
Included in Package	Strike Plate
Included in Package	Round Grommet
Included in Package	Locking Latches (with 2 keys each)
Included in Package	Casters
Included in Package	Rear Panel
Included in Package	Front/Rear Support
Included in Package	Front Door
Included in Package	Rack Top
Included in Package	M6x12 Screws
Included in Package	Connecting Bolts



Included in Package	Cams
Included in Package	Instruction Manual
Included in Package	Dowel Pins
Included in Package	M4x12 Screws
Included in Package	M5x12 Screws
Included in Package	M6x15
Included in Package	M5 Screws
Included in Package	M5 Cage Nuts

---

***\*Product appearance and specifications are subject to change without notice.***

