

2m USB C to Lightning Cable - Durable Black USB Type C to Lightning Connector Fast Charge & Sync Charging Cord, Rugged w/Aramid Fiber Apple MFI Certified iPhone 11 iPad Air

Product ID: RUSBCLTMM2MB



This 2 m (6.5 ft.) black USB C to Lightning cable withstands the daily demands of charging and syncing your iPad, iPhone or other mobile devices featuring the Lightning connector. Tested to endure strenuous wear and tear and winter and summer in-car use, the strong and rugged cable is a must-have for both business and consumer applications.

The durable USB C to Lightning cable has aramid fiber reinforcement that shelters it from the stress of frequent bends and twists. This also lets the heavy duty cable flex without over-stretching and strengthens the core of the cable.

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI (electromagnetic interference) protection with aluminum-mylar foil with braided shielding
- TPE (thermoplastic elastomer) cable jacket is softer and more flexible than a standard PVC cable and environmentally friendly

The reinforced cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle. Plus, the improved inner molding resists cracking and reduces cable damage.

- Lightning connector provides 12W so your charger can charge your iOS devices
- Metal shield protects circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

RUSBCLTMM2MB is an Apple MFi certified Lightning cable backed by a StarTech.com 2-year warranty.

Note: DuPont and Kevlar are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.

Certifications, Reports and Compatibility

Applications

- Charge and sync your Lightning mobile devices

Features

- **APPLE MFI CERTIFIED:** USB C to lightning cable to safely charge & sync lightning devices; supports fast charging using Power Delivery chargers like Apple 18W, 29W, 30W, 61W, 87W or 96W USB-C power adapters
- **FLEXIBLE CABLE:** TPE jacket absorbs stress of frequent bends without damaging the core of the cable. Durable wire & connector protects this charge & sync cable from wear & tear of frequent in-car use
- **FLEXIBLE CABLE:** Built with TPE jacket to absorb the stress of frequent bends without damaging the core of the cable. TPE is non-toxic, halogen free & RoHS certified for environmental sustainability
- **FAST CHARGE:** Up to 18W with PD chargers and USB-C or Thunderbolt 3 laptops to charge iPhone 8, iPhone 8 Plus, iPhone 11 Pro, iPhone 11, iPhone XR, iPad Air, iPad (3rd gen), iPad Mini (5th gen)
- **CABLE SPECS:** Length: 2m (6ft) Color: Black Connectors: USB-C to Lightning Performance: USB 2.0 Reinforcement: Aramid Fiber Jacket Type: TPE Shielding: EMI Protection Warranty: 2-Year

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid


Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	Apple Lightning Connector (8-pin)
	USB Type-C (24-pin) USB 2.0 (480Mbps)

Physical Characteristics



Color	Black
Connector Style	Straight
Wire Gauge	22/32 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.5 in [12.0 mm]
Product Height	0.2 in [6.2 mm]
Weight of Product	0.9 oz [26.0 g]

Packaging Information

Package Length	7.2 in [18.3 cm]
Package Width	3.0 in [75.0 mm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	1.6 oz [46.0 g]

What's in the Box

Included in Package	2 m Lightning Cable
---------------------	---------------------

**Product appearance and specifications are subject to change without notice.*

