

## 3.5in Black USB 3.0 External SATA III Hard Drive Enclosure with UASP for SATA 6 Gbps – Portable External HDD

**Product ID:** S3510BMU33



The S3510BMU33 Black USB 3.0 Hard Drive Enclosure with UASP lets you connect a 3.5in SATA III hard drive (HDD) through an available USB port. The enclosure delivers optimal performance with a USB 3.0 connection, but is backward compatible with USB 2.0/1.1 host connections as well.

Enhanced with UASP (USB Attached SCSI Protocol), this 3.5" SATA III enclosure performs up to 70% faster than conventional USB 3.0 when paired with a UASP-enabled host controller. Using a more efficient protocol than the traditional USB BOT (Bulk-Only Transport), UASP reduces latency, significantly increasing transfer speeds and reducing processor usage to utilize the full potential of your SATA III hard drives. See our UASP testing results below for further details.

With support for SATA I/II/III, and large capacity drives (tested up to 4TB) this HDD enclosure is compatible with virtually any 3.5in SATA hard drive, and can greatly increase the storage/backup capabilities of your computer.

The USB 3.0/SATA III enclosure features high quality aluminum construction, ensuring durability.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

UASP is supported in Windows 8, Mac OSX (10.8 or above), and Linux. In testing UASP performs with a 70% faster read speed and 40% faster write speed over traditional USB 3.0 at peak performance.

At the same peak in testing UASP also shows an 80% reduction in required processor resources.

Testing results were obtained using an Intel Ivy Bridge system, a UASP enabled StarTech.com enclosure, and a SATA III solid state drive.

## Certifications, Reports and Compatibility

## Applications

- Take advantage of new laptops and desktops with USB 3.0 (UASP) connectivity
- Upgrade from a USB 2.0 drive enclosure to faster USB 3.0
- Create a fast, portable external storage solution for desktops, laptops or netbooks
- Add-on extra storage to almost any USB enabled computer system
- Backup important data to an external storage device
- Share large files between computers quickly and securely without a network
- Retrieve data from an old SATA drive, or turn the unused drive into additional external storage space
- Turn a high capacity SATA hard drive into portable, external storage

## Features

- SuperSpeed USB 3.0 compliant host interface supporting data transfer rates up to 5Gbps
- Light-weight and durable aluminum enclosure
- Power/Activity LED indicator
- Compatible with SATA revision I/II/III (1.5/3.0/6.0 Gbps) drives
- Plug-and-Play and Hot-Swap compatible
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480Mbps
- Compliant with USB Attached SCSI Protocol (UASP) Transport Specifications
- Vented Drive Tray

---

### Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 3.0
Number of Drives	1
Drive Size	3.5in
Compatible Drive Types	SATA
Drive Installation	Fixed

Chipset ID ASMedia - ASM1053 - 6G

---

**Performance**

Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Type and Rate	SATA III (6 Gbps)
Hardware Raid Supported	No
Max Drive Capacity	Currently tested with up to 4TB 7200 RPM hard drives

---

**Connector(s)**

Drive Connectors	SATA Data & Power Combo (7+15 pin)
Host Connectors	USB Type-B (9 pin) USB 3.0

---

**Software**

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

**Special Notes / Requirements**

System and Cable Requirements	Available USB port
-------------------------------	--------------------

---

**Indicators**

LED Indicators	Power & Activity
----------------	------------------

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.6 A
Output Voltage	12V DC
Output Current	2 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	24



---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 65C (14F to 149F)
Humidity	Operation Humidity: 10% ~ 90% RH Storage Humidity: 5% ~ 95% RH

---

**Physical Characteristics**

Color	Black
Material	Aluminum and Plastic
Product Length	7.5 in [19.2 cm]
Product Width	1.2 in [31.4 mm]
Product Height	4.5 in [11.5 cm]
Weight of Product	11.0 oz [311 g]

---

**Packaging Information**

Package Length	5.3 in [13.4 cm]
Package Width	8.9 in [22.5 cm]
Package Height	4.2 in [10.6 cm]
Shipping (Package) Weight	27.8 oz [787 g]

---

**What's in the Box**

Included in Package	3.5" USB 3.0 SATA III HDD Enclosure
	Product Manual
	Screw Kit
	USB 3.0 Cable
	Universal Power Adapter (NA / UK / EU)
	HDD Stand

---

***\*Product appearance and specifications are subject to change without notice.***

