

## USB 3.0 eSATA Hard Drive Enclosure - Trayless 3.5" SATA III HDD Enclosure - SATA 6 Gbps - Black

Produkt ID: S3510BMU33ET



The S3510BMU33ET Removable Hard Drive Enclosure lets you connect a 3.5" SATA hard drive through an available USB 3.0 or eSATA port, with a tray-less design that makes hot-swapping easy.

For fast performance and efficient data transfers, when connected through eSATA, the enclosure supports full SATA III transfer speeds -- up to 6 Gbps. For universal compatibility, the enclosure can be connected through USB 3.0 with transfer speeds up to 5 Gbps plus support for UASP, which supports performance up to 70% faster than conventional USB 3.0 when paired with a UASP-enabled host controller to utilize the full potential of your SATA III hard drives. See our UASP testing results below for further details.

The HDD enclosure offers a versatile solution for increasing the storage/backup capabilities of your computer, with support for hard drives at capacities of up to 4TB, and the ability to easily hot-swap between drives. Plus, to maximize both durability and reliability, the enclosure features high-quality aluminum construction.

To ensure compatibility with your computer system, the S3510BMU33ET supports all of the leading operating systems, including: Microsoft Windows® (8/7/Vista/XP/Server 2008/Server 2003), Apple® OSX (10.9/10.8/10.7/10.6), Linux, and Google Chrome OS™.

It is backed by a StarTech.com 2-year warranty and free lifetime technical support.

UASP is supported in Windows 8, Mac OSX (10.8 or above), and Linux. In testing UASP performs with a 70% faster read speed and 40% faster write speed over traditional USB 3.0 at peak performance.

At the same peak in testing UASP also shows an 80% reduction in required processor resources.

Testing results were obtained using an Intel® Ivy Bridge system, a UASP enabled StarTech.com Enclosure, and a SATA III solid state drive.

## Certifikat, rapporter och kompatibilitet

### Användning

- Retrieve data from an old SATA drive, or turn the unused drive into additional external storage space
- Upgrade from a USB 2.0 drive enclosure to faster USB 3.0
- Share large files between computers quickly and securely without a network
- Hot-swap drives using a single enclosure instead of having to swap separate enclosures

### Funktioner

- UASP Compatible
- eSATA or USB Host Connection
- Trayless Aluminum Enclosure
- Compatible with SATA revision I/II/III (1.5/3.0/6.0 Gbps)
- Compatible with USB 3.0/2.0/1.1 (5Gbps/480Mbps/12Mbps)
- Plug-and-Play and Hot-Swap Compatible

---

#### Hårdvara

Garantipolicy	2 Years
Gränssnitt	USB 3.0 eSATA USB 3.0 & eSATA
Antal enheter	1
Enhetsstorlek	3.5in
Enhetsstyp	SATA
Enhetsinstallation	Löstagbar

Antal interna 3,5 tums fack 1

Chipset-ID ASMedia - ASM1053 - 6G

---

Prestanda

Maximal dataöverföringshastighet	5 Gbps
Typ och hastighet	USB 3.0 - 5 Gbit/s
UASP-stöd	Ja
Typ och hastighet	SATA III (6 Gbps)
Hot swap-förmåga	Ja

---

Kontakt(er)

Enhetskontakter	SATA data- & ström-kombo (7+15-stifts)
Värdkontakter	eSATA (7-stifts, data) USB Type-B (9-stifts) USB 3.0

---

Mjukvara

OS-kompatibilitet	OS independent; No software or drivers required
-------------------	---

---

Indikatorer

LED-indikatorer	Power/Activity
-----------------	----------------

---

Ström

Power Source	AC-adapter medföljer
Inspänning	110V-240V AC
Inström	0.8A
Utspänning	12V DC
Utström	2A
Polaritet på mittpol	Positiv
Kontakttyp	M



Strömförbrukning 24

---

Miljö

Drifttemperatur 5°C to 40°C (41°F to 104°F)  
Förvaringstemperatur 5°C to 40°C (41°F to 104°F)  
Luftfuktighet 20%RH ~ 80%RH

---

Utseende

Produktlängd 7.9 in [20 cm]  
Produktbredd 1.7 in [43 mm]  
Produkthöjd 5.4 in [13.8 cm]  
Produktvikt 28.9 oz [820 g]

---

Förpackning

Package Length 8.9 in [22.5 cm]  
Package Width 7.1 in [18 cm]  
Package Height 4.5 in [11.5 cm]  
Fraktvikt (förpackning) 3.1 lb [1.4 kg]

---

Vad det är i lådan

Ingår i paketet  
HDD Enclosure  
USB 3.0 Cable  
eSATA Cable  
Universal Power Adapter (NA/UK/EU)  
Instruction Manual

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

