

1m Infiniband External SAS Cable - SFF-8470 to SFF-8470

Product ID: SAS7070S100



The SAS7070S100 1-meter Serial-Attached-SCSI (SAS) Cable features two Infiniband 4x plugs with thumbscrews, providing reliable, high-performance drive and backplane connectivity.

The SFF-8470 to SFF-8470 is backed by a lifetime warranty, ensuring optimized functionality and durability.

StarTech.com's SAS7070S100 1m SAS cable is equivalent to HP part number 389665-B21.

Certifications, Reports and Compatibility

Applications

- Connect SAS Backplanes to SATA Drives

Features

- Compatible with many servers, including:
 - Dell PowerVault MD1120
 - HP ProLiant DL140 G2
 - HP ProLiant DL320 G3
 - HP ProLiant DL360 G4
 - HP ProLiant DL360 G4p
 - HP ProLiant DL385
 - HP ProLiant DL580 G2
 - HP ProLiant DL580 G3
 - HP ProLiant ML310 G2
 - HP ProLiant ML350 G4
 - HP ProLiant ML350 G4p
 - HP ProLiant ML370 G4
 - HP ProLiant ML570 G2
 - HP ProLiant ML570 G3
 - HP Smart Array P600 Controller
 - HP StorageWorks Modular Smart Array 50
- Durable metal connectors
- Infiniband plug with latches for secure connections
- Supports data transfer rates up to 6 Gbps

Hardware

Warranty	Lifetime
Number of Conductors	32
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Triple Shielding (Dual foil and braid)

Connector(s)

Connector A	SFF-8470 (32 pin, Infiniband, External SAS)
Connector B	SFF-8470 (32 pin, Infiniband, External SAS)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	0.0 oz [0.0 g]

Packaging Information

Package Length	5.4 in [13.8 cm]
Package Width	0.6 in [15.0 mm]
Package Height	11.0 in [28.0 cm]
Shipping (Package) Weight	7.1 oz [200.0 g]

What's in the Box

Included in Package	100cm Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8470
---------------------	---

**Product appearance and specifications are subject to change without notice.*