

3.5" SATA Hard Drive Enclosure - eSATA / USB 3.0 - Trayless, TAA-Compliant

Product ID: S351BMU33ET



This eSATA enclosure for 3.5 in. SATA HDDs is perfect for office, government, medical, and other personnel who require quick and easy access to important data and files. It is ideal if you need easy access to your data or need to back up, archive, or recover data and multimedia content.

Multiple connectivity options

The external hard drive enclosure supports USB 3.0, also known as USB 3.1 Gen 1, and eSATA, allowing you to access your data through your preferred interface. For fast performance and efficient data transfers, when connected through eSATA, the enclosure supports full SATA III transfer speeds - up to 6Gbps.

For universal compatibility, the enclosure can be connected through USB 3.0 with transfer speeds up to 5Gbps, plus support for UASP. The HDD enclosure lets you connect a SATA III (6Gbps) hard drive, but is also compatible with SATA I and II.

Ease of use

The hard drive enclosure allows you to swap drives in and out as needed with the trayless design. The enclosure is simple to set up and easy to use, with its plug-and-play functionality. It's also equipped with an LED light to indicate power and activity.

Compact design works great with your Mac or PC

With a sleek, compact style, this hard drive enclosure is a perfect desktop companion for your Mac or PC. It occupies minimal space, and features a fanless design that keeps the enclosure quiet so you to focus on what's important.

The S351BMU33ET is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Retrieve data from an old SATA drive, or turn the unused drive into additional external storage space
- Hot-swap drives using a single enclosure instead of having to swap separate enclosures
- Upgrade from a USB 2.0 drive enclosure to faster USB 3.0
- Share large files between computers quickly and securely without a network connection
- Perfect for creative professionals, office, government, and medical personnel, sales executives, teachers, and research scientists who require access to important data and files

Features

- Easily swap drives in and out as needed with trayless design
- Quickly access important files with this removable hard drive enclosure for 3.5" SATA HDDs
- Access your files via your preferred interface with support for USB 3.0 and eSATA
- 4Kn support
- Supports SATA I, II, and III (up to 6Gbps)
- SMART support
- TRIM support
- Easy to set up with plug-and-play functionality
- Insertion rating of 50,000 cycles
- Keep your desk looking organized with a sleek, black metal design

Hardware

Warranty	2 Years
Fan(s)	No

Interface	USB 3.0 & eSATA
Bus Type	USB 3.0 & eSATA
Number of Drives	1
Drive Size	3.5in
Compatible Drive Types	SATA
Drive Installation	Removable
Number of internal 3.5 inch bays	1
Chipset ID	ASMedia - ASM1153E ASMedia - ASM1456

Performance

Maximum Data Transfer Rate	6 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
TRIM Support	Yes
4Kn Support	Yes
S.M.A.R.T. Support	Yes
Type and Rate	SATA III (6 Gbps)
Max Drive Capacity	Currently tested with up to 10TB 7200 RPM hard drives
Hot Swap Capability	Yes
Insertion Rating	50,000 cycles

Connector(s)

Drive Connectors	1 - SATA Data & Power Combo (7+15 pin)
Host Connectors	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps) 1 - eSATA (7 pin, Data)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	Windows 7 and earlier Windows versions do not support TRIM with USB to SATA devices.
------	--

Indicators

LED Indicators	1 - Power/Activity
----------------	--------------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.8A
Output Voltage	12V DC
Output Current	2000mA
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	24

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 55C (-4F to 131F)
Humidity	5% to 65%

Physical Characteristics

Color	Black
Material	Steel
Product Length	8.3 in [21.0 cm]
Product Width	5.3 in [13.4 cm]
Product Height	1.5 in [3.8 cm]
Weight of Product	18.4 oz [520.0 g]

Packaging Information

Package Quantity	1
Package Length	6.3 in [15.9 cm]
Package Width	9.6 in [24.4 cm]
Package Height	4.1 in [10.3 cm]
Shipping (Package) Weight	2.3 lb [1.0 kg]

What's in the Box

Included in Package	1 - drive enclosure
	1 - enclosure stand
	1 - USB 3.0 cable
	1 - eSATA cable
	1 - Power Adapter (NA)
	1 - quick-start guide

****Product appearance and specifications are subject to change without notice.***