

## 24in SATA to Left Angle SATA Serial ATA Cable

Produkt ID: SATA24LA1



The SATA24LA1 Left Angle (90-degree) SATA Cable features a standard (straight) SATA receptacle as well as a left-angled SATA receptacle, providing a simple 24-inch connection to a Serial ATA drive, with full SATA 3.0 bandwidth support of up to 6Gbps when used with SATA 3.0 compliant drives.

The left-angled SATA connection enables you to plug in your Serial ATA hard drive in hard to reach areas or tight spaces, while the low profile and flexible design of the cable improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance and reliability this 24" SATA cable is backed by our lifetime warranty.

As an alternative, StarTech.com also offers a 24in Right Angle SATA cable (SATA24RA1), which provides the same simple installation as this left angled SATA cable, but allows the cable to connected to the SATA drive from the opposite direction.

## Certifikat, rapporter och kompatibilitet



## Användning

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications

- High-end workstation drive installations
- Connections to SATA Drive Arrays

## Funktioner

- 1x SATA connector
- 1x Left-angled/90-degree SATA connector
- Supports full SATA 3.0 6Gbps bandwidth
- Compatible with both 3.5" and 2.5" SATA hard drives
- Provides 24" in cable length

### Hårdvara

|                |                          |
|----------------|--------------------------|
| Garantipolicy  | Lifetime                 |
| Kabelmanteltyp | PVC - Polyvinyl Chloride |

### Prestanda

|                   |                   |
|-------------------|-------------------|
| Typ och hastighet | SATA III (6 Gbps) |
|-------------------|-------------------|

### Kontakt(er)

|             |                           |
|-------------|---------------------------|
| Connector A | 1 - SATA (7-stifts, data) |
| Connector B | 1 - SATA (7-stifts, data) |

### Utseende

|            |                         |
|------------|-------------------------|
| Färg       | Röd                     |
| Kontakttyp | Rak till vänstervinklad |
| Kabellängd | 24.0 in [609.6 mm]      |

### Förpackning

|                   |                  |
|-------------------|------------------|
| Förpackningsantal | 1                |
| Paketets längd    | 4.9 in [12.5 cm] |
| Paketets bredd    | 0.5 in [13 mm]   |

Paketets höjd 8.7 in [22 cm]

Fraktvikt (förpackning) 0.0 lb [0.0 kg]

---

Vad det är i lådan

|                 |                                                   |
|-----------------|---------------------------------------------------|
| Ingår i paketet | 1 - 24in SATA to Left Angle SATA Serial ATA Cable |
|-----------------|---------------------------------------------------|

---

Warranty  
Information

|          |           |
|----------|-----------|
| Warranty | Livslängd |
|----------|-----------|

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.