

## 36in SATA Serial ATA Cable

Produkt ID: SATA36



The SATA36 Serial ATA Cable features two 7-pin data receptacles and supports full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives.

Featuring a low profile, yet durable construction, the flexible design improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance and reliability this 36" SATA cable is backed by our lifetime warranty.

## Certifikat, rapporter och kompatibilitet

### Användning

- Installing Serial ATA hard drives, and DVD drives
- Server and storage subsystem applications
- High-end workstation drive installations
- Connections to SATA Drive Arrays

### Funktioner

- Compatible with both 3.5" and 2.5" SATA hard drives

- Supports full SATA 3.0 6Gbps bandwidth
- Provides 36" in cable length

---

#### Hårdvara

|                |                          |
|----------------|--------------------------|
| Garantipolicy  | Lifetime                 |
| Kabelmanteltyp | PVC - Polyvinyl Chloride |

---

#### Prestanda

|                   |                   |
|-------------------|-------------------|
| Typ och hastighet | SATA III (6 Gbps) |
|-------------------|-------------------|

---

#### Kontakt(er)

|             |                       |
|-------------|-----------------------|
| Connector A | SATA (7-stifts, data) |
| Connector B | SATA (7-stifts, data) |

---

#### Miljö

|                      |                               |
|----------------------|-------------------------------|
| Drifttemperatur      | 20°C to 80°C (68°F to 176°F)  |
| Förvaringstemperatur | 24°C to 25°C (75.2°F to 77°F) |
| Luftfuktighet        | 50% relative humidity         |

---

#### Utseende

|              |                   |
|--------------|-------------------|
| Färg         | Röd               |
| Kontakttyp   | Rak               |
| Kabellängd   | 36.0 in [91.4 cm] |
| Produktlängd | 36.0 in [91.4 cm] |
| Produktbredd | 0.6 in [14 mm]    |
| Produkt höjd | 0.2 in [6.2 mm]   |
| Produktvikt  | 0.9 oz [26.0 g]   |

---

#### Förpackning

|                |                  |
|----------------|------------------|
| Package Length | 5.0 in [12.8 cm] |
| Package Width  | 8.6 in [22.0 cm] |



Package Height 0.0 in [0.6 mm]

Fraktvikt  
(förpackning) 1.1 oz [31.0 g]

---

Vad det är i  
lådan

Ingår i paketet 36in SATA Serial ATA Cable

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

