

5.25in Silver eSATA USB 2.0 to SATA Optical Drive Enclosure

Product ID: SAT5210U2EGB



This versatile drive enclosure offers a cost-effective way to turn any SATA II 3.5in hard drive (up to 1.5TB) or 5.25in optical drive (Blu-ray DVDRW, CD-ROM, CD-RW, DVD-ROM, DVD-RW), into an external solution.

The drive enclosure can be connected to a host computer through either USB 2.0 or eSATA, and supports the full capability of both interfaces (maximum data transfer capability up to 3 Gbps with eSATA, up to 480 Mbps through USB 2.0).

To help ensure dependable drive operation, the enclosure provides a sturdy yet attractive aluminum casing and a 40mm fan to help keep the installed hard drive or optical drive cool.

Drives can be installed in the enclosure in minutes, and the enclosure features the added convenience of a stereo headphone jack for computer-free CD playback.

Certifications, Reports and Compatibility

Applications

- Add external DVD/CD burning capability to notebooks and desktops with USB or eSATA connectivity.
- Turn any internal SATA I/II drive into an external DVD/CD drive or storage.

Features

- Allows 3.5" SATA I/II (SATA 150/300) Hard Drives (including 1.5 terabyte) and 5.25" SATA Optical Drive in one enclosure.

- Aluminum casing and 40mm fan for maximum heat dissipation
- Equipped with USB 2.0 and eSATA interfaces for maximum data transfer, and versatility
- Full plug and play support through USB 2.0 interface
- Quick and easy installation

General

UPC	065030830720
Warranty	2 Years

Power

Power Source	AC Adapter Included
Center Tip Polarity	Positive

Physical & Environmental

Color	Silver
Material	Aluminum
Product Length	10.2 in [25.9 cm]
Product Width	6.5 in [16.6 cm]
Product Height	2.3 in [58 mm]
Weight of Product	32.8 oz [930 g]

Performance

General Specifications	Connectors: 1x SATA Power 15 Pin Female 1x USB B Male Host: 1x eSATA Data Male Internal Drive: 1x SATA Data 7 Pin Female Maximum Data Transfer Rate: Up to 3 Gbps with eSATA, 480 Mbps with USB 2.0 OS Support: Windows 98SE/ME/2000/XP/VISTA/Mac OS 9x and up
------------------------	---

Supported Hard Drive: 3.5" SATA I/II (SATA150 and SATA300)
Hard Drive up-to 1.5TB

Supported Optical Drive: SATA I/II (SATA150 and SATA300)
CD-ROM/RW, DVD ROM/RW, Blu-Ray DVD ROM/Writer
(Tested with a Lite-On LH-2B1S Internal Blu-Ray SATA Drive)

Hardware

Fans	1 - 40 mm
LED Indicators	1 - Power LED: Green

Packaging & In-the-Box

Included in Package	1 - Drive Enclosure
	1 - USB Cable
	1 - Power Adapter
	1 - Driver CD Rom
	1 - Manual
Package Width	12.6 in [32 cm]
Package Depth	2.9 in [73 mm]
Package Height	10.5 in [26.7 cm]
Shipping (Package) Weight	3.4 lb [1.6 kg]

****Product appearance and specifications are subject to change without notice.***