

USB to SATA External Hard Drive Docking Station for 2.5 or 3.5in HDD

Product ID: SATADOCKU2



This external hard drive dock adapter functions as a SATA HDD docking station - providing full, instant access to any 2.5in or 3.5in SATA (SATA, SATA II, SATA III) hard drive or solid state drive - without having to mount the hard drive in a computer or install it in an enclosure! Large capacity drives (tested with up to 4TB 3.5" and 1TB 2.5" drives) can be used to greatly enhance your computer's storage/backup capabilities.

Simply connect the hard drive dock to a host computer through USB 2.0, then insert a SATA hard drive into the dock whenever needed. To uninstall or swap the hard drive, just remove it from the dock!

The USB to SATA External HDD Dock Adapter supports plug and play hard drive installation on most operating systems, and offers data transfer speeds of up to 480Mbps - providing a convenient alternative to external hard drive enclosures and saving the time needed to prepare the drive for conventional installation. Double the value of this hard drive docking station, using a SATA to IDE hard drive adapter (SAT2IDEADP), which enables you to use any 2.5 or 3.5in IDE hard drive in a SATA hard drive dock slot.

Certifications, Reports and Compatibility

Applications

- Access spare or removed 2.5/3.5" drives quickly to retrieve data from
- Data recovery specialists who need quick access to drives for imaging
- Backup data quickly to an external drive for archiving
- Technicians who regularly test or benchmark different hard drives

Features

- Top slot loading design with drive door
- Power/Activity LED indicator
- High Speed USB 2.0 compliant host interface, with support for transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" or 3.5" form factor hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible
- Compact desktop style form factor

Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 2.0
Number of Drives	1
Drive Size	2.5in & 3.5in
Compatible Drive Types	SATA

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
UASP Support	No
Max Drive Capacity	Currently tested with up to 4TB 5400 RPM 3.5" hard drives and 1TB 5400 RPM 2.5" hard drive
Insertion Rating	15,000 Cycles


Connector(s)

Drive Connectors	SATA Data & Power Combo (7+15 pin)
Host Connectors	USB B (4 pin)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements



Note Advance Format drives are not fully supported

Indicators

LED Indicators Solid - Power, Blinking - Activity

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Output Voltage 12V DC

Output Current 2 A

Center Tip Polarity Positive

Plug Type M

Physical Characteristics

Color Black

Material Plastic

Product Length 5.5 in [14 cm]

Product Width 3.6 in [91 mm]

Product Height 2.2 in [55 mm]

Weight of Product 7.8 oz [220 g]

Packaging Information

Package Length 6.7 in [17 cm]

Package Width 3.5 in [90 mm]

Package Height 6.7 in [17 cm]

Shipping (Package) Weight 18.4 oz [520 g]

What's in the Box

Included in Package SATA hard drive docking station

USB Cable



Power Adapter

Instruction Manual

****Product appearance and specifications are subject to change without notice.***

