

USB 3.0 SATA Hard Drive Duplicator & Eraser Dock - Standalone 2.5/3.5in HDD & SSD Eraser and Cloner

Product ID: SATDOCK2REU3



The SATDOCK2REU3 USB 3.0 Standalone Duplicator and Eraser Dock lets you connect your 2.5in/3.5in SATA HDDs or SSDs through SuperSpeed USB 3.0, with the ability to swap drives in and out as needed. The dock also functions as a standalone drive duplicator and eraser – an efficient and versatile solution for external drive management.

Featuring standalone Sector by Sector hard drive duplication with built-in LED progress bar, and support for 2 drive single pass over writing the SATDOCK2REU3 is a user-friendly all-in-one solution for any application requiring hard drive duplication or erasing.

With support for SATA I/II/III, and large capacity drives (tested up to 4TB) this HDD/SSD docking station is compatible with virtually any SATA hard drive, and greatly increases the storage/backup capabilities of your computer.

Extend the value of this hard drive docking station further with the addition of our [%product id="SAT2IDEADP" text="SATA to IDE Hard Drive Adapter"](SAT2IDEADP), allowing easy insertion of any 2.5 or 3.5in. IDE hard drive into a SATA hard drive dock.

The SATDOCK2REU3 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- System administrators who need quick access to drives for imaging

- Data Archiving
- Technicians who regularly test or benchmark different hard drives and need to swap between them
- Forensic investigators who require disk sector imaging/cloning to create an exact replica of a source drive onto a different drive
- Professionals who require identical backups for when data integrity is crucial, such as data recovery
- Cloning hard drives that contain hidden partitions, that some software disk cloning programs may skip
- IT administrators that wish to quickly clear/erase a drive in preparation for use in other applications
- Data recovery specialists who need quick access to drives to recover/retrieve data

Features

- Supports 2.5in and 3.5in form factor SATA hard drives (HDD) and solid state drives (SSD)
- SuperSpeed USB 3.0 compliant host interface, with up to 5 Gbps of data bandwidth
- Stand alone single pass overwrite erase
- Universal Power Adapter (NA/UK/EU)
- Plug-and-Play and Hot-Swap compatible
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480Mbps
- Standalone Sector-by-Sector hard drive duplication
- Built-in LED progress bar
- Supports SATA revision I/II/III (1.5/3.0/6.0 Gbps) drives

Hardware	Warranty	2 Years
	Fan(s)	No
	Interface	USB 3.0
	Number of Drives	2
	Drive Size	2.5in & 3.5in
	Compatible Drive Types	SATA
	Drive Installation	Removable
	Chipset ID	Prolific - PL2775
Performance	Maximum Data Transfer Rate	3Gbps
	Type and Rate	USB 3.0 - 5 Gbit/s
	Type and Rate	SATA II (3 Gbps)
	Duplication Modes	Sector by Sector (Whole Drive)
	Duplication Speed	11GBpm
	Erase Modes	1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear)
	Max Drive Capacity	Currently tested with up to 4TB 7200 RPM 3.5" hard drives and 1TB 7200 RPM 2.5" hard drives
Connector(s)	Drive Connectors	SATA Data & Power Combo (7+15 pin)
	Host Connectors	USB Type-B (9 pin) USB 3.0

Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	Note	Destination drive must be the same size or larger than the source drive
Indicators	LED Indicators	Link / 25%
	LED Indicators	Power / 50%
	LED Indicators	HDD1 / 75%
	LED Indicators	HDD2 / 100%
Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	1.2A
	Output Voltage	12V DC
	Output Current	3000mA
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	36
Environmental	Operating Temperature	0C to 85C (32F to 185F)
	Storage Temperature	-10C to 95C (14F to 203F)
	Humidity	5-90%
Physical Characteristics	Product Length	5.0 in [1.3 cm]
	Product Width	4.1 in [1.0 cm]
	Product Height	2.4 in [62 mm]
	Weight of Product	15.0 oz [424 g]
Packaging Information	Package Length	7.7 in [2.0 cm]
	Package Width	6.5 in [1.6 cm]
	Package Height	5.1 in [1.3 cm]
	Shipping (Package) Weight	31.2 oz [885 g]
What's in the Box	Included in Package	HDD Dock
	Included in Package	User Manual

Included in Package	Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand
Included in Package	USB 3.0 Cable

****Product appearance and specifications are subject to change without notice.***

