

USB 3.0 SATA Hard Drive Duplicator & Eraser Dock - Standalone 2.5/3.5in HDD & SSD Eraser and Cloner

Produkt ID: SATDOCK2REU3



The SATDOCK2REU3 USB 3.0 Standalone Duplicator and Eraser Dock lets you connect your 2.5in/3.5in SATA HDDs or SSDs through SuperSpeed USB 3.0, with the ability to swap drives in and out as needed. The dock also functions as a standalone drive duplicator and eraser – an efficient and versatile solution for external drive management.

Featuring standalone Sector by Sector hard drive duplication with built-in LED progress bar, and support for 2 drive single pass over writing the SATDOCK22EU3 is a user-friendly all-in-one solution for any application requiring hard drive duplication or erasing.

With support for SATA I/II/III, and large capacity drives (tested up to 4TB) this HDD/SSD docking station is compatible with virtually any SATA hard drive, and greatly increases the storage/backup capabilities of your computer.

Extend the value of this hard drive docking station further with the addition of our SATA to IDE Hard Drive Adapter (SAT2IDEADP), allowing easy insertion of any 2.5 or 3.5in. IDE hard drive into a SATA hard drive dock.

The SATDOCK2REU3 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- System administrators who need quick access to drives for imaging

- Data Archiving
- Technicians who regularly test or benchmark different hard drives and need to swap between them
- Forensic investigators who require disk sector imaging/cloning to create an exact replica of a source drive onto a different drive
- Professionals who require identical backups for when data integrity is crucial, such as data recovery
- Cloning hard drives that contain hidden partitions, that some software disk cloning programs may skip
- IT administrators that wish to quickly clear/erase a drive in preparation for use in other applications
- Data recovery specialists who need quick access to drives to recover/retrieve data

Funktioner

- Supports 2.5in and 3.5in form factor SATA hard drives (HDD) and solid state drives (SSD)
- Standalone Sector-by-Sector hard drive duplication
- Stand alone single pass overwrite erase
- SuperSpeed USB 3.0 compliant host interface, with up to 5 Gbps of data bandwidth
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480Mbps
- Supports SATA revision I/II/III (1.5/3.0/6.0 Gbps) drives
- Plug-and-Play and Hot-Swap compatible
- Universal Power Adapter (NA/UK/EU)
- Built-in LED progress bar

Hårdvara

Garantipolicy	2 Years
Fläkt(ar)	Nej
Gränssnitt	USB 3.0
Antal enheter	2
Enhetsstorlek	2.5in & 3.5in

Enhetstyp	SATA
Enhetsinstallation	Löstagbar
Chipset-ID	Prolific - PL2775

Prestanda

Maximal dataöverföringshastighet	3Gbps
Typ och hastighet	USB 3.0 - 5 Gbit/s SATA II (3 Gbps)
Duplication Speed	11GBpm
Raderingslägen	1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear)
Duplication Modes	Sector by Sector (Whole Drive)
Maximal enhetskapacitet	Currently tested with up to 4TB 7200 RPM 3.5" hard drives and 1TB 7200 RPM 2.5" hard drives

Kontakt(er)

Enhetskontakter	SATA data- & ström-kombo (7+15-stifts)
Värdkontakter	USB Type-B (9-stifts) USB 3.0

Mjukvara

OS-kompatibilitet	OS independent; No software or drivers required
-------------------	---

Särskilda anmärkningar/krav

Obs.	Destination drive must be the same size or larger than the source drive
------	---

Indikatorer

LED-indikatorer	Link / 25%
	Power / 50%
	HDD1 / 75%
	HDD2 / 100%

Ström

Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	1.2A
Utspänning	12V DC
Utström	3000mA
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	36

Miljö

Drifttemperatur	0°C to 85°C (32°F to 185°F)
Förvaringstemperatur	-10°C to 95°C (14°F to 203°F)
Luftfuktighet	5-90%

Utseende

Produktlängd	5.0 in [12.8 cm]
Produktbredd	4.1 in [10.3 cm]
Produkt höjd	2.4 in [62 mm]
Produktvikt	15.0 oz [424 g]

Förpackning

Package Length	7.7 in [19.5 cm]
Package Width	6.5 in [16.5 cm]
Package Height	5.1 in [13 cm]
Fraktvikt (förpackning)	31.2 oz [885 g]

Vad det är i lådan

Ingår i paketet	HDD Dock USB 3.0 Cable
-----------------	---------------------------



Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand

User Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

