

2.5" Hot Swap Hard Drive Tray

Product ID: SATSASTRX25



This 2.5" hard drive tray lets you add even more flexibility to how you manage your data storage with the SATSASBP425 and SATSASBP125 series backplanes.

This spare drive tray can help you save time in a fast-paced work environment. It's interchangeable with trays from the StarTech.com single-bay backplane (SATSASBP125) and the four-bay backplane (SATSASBP425), giving you an extra tray in addition to the trays you're already using, to create expandable storage or as part of a rotating back-up solution.

The drive tray supports both SAS and SATA 2.5" drives, ranging from 5 to 15mm in height. To maximize the performance of your hard drives, the single and quad-bay backplanes support SAS II and SATA III enabling file transfer speeds up to 6 Gbps when paired with a compatible controller.

The durable aluminum drive tray is designed for long-lasting performance. The venting helps to ensure proper air flow and maximize heat dissipation, to help keep your drives running at optimal temperatures.

The SATSASTRX25 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Be ready with multiple replacement drives for the SATSASBP125 and SATSASBP425 mobile rack backplanes
- Keep spare or replacement hard drives on hand for expandable storage
- Use the tray for extra hard drives for rotating backup solutions

Features

- Swap drives quickly with this drive tray for 2.5" SSD/HDDs
- Interchangeable with the single-bay (SATSASBP125) and quad-bay (SATSASBP425) backplanes
- Compatible with 2.5" SAS or SATA SSDs and HDDs 5-15mm
- Durable aluminum tray with ventilation
- Flammability rating of UL 94-V0

Hardware

Warranty	2 Years
Fan(s)	No
Number of Drives	1
Drive Size	2.5in
Compatible Drive Types	SAS & SATA
Supported Drive Height(s)	5mm
	7mm
	9.5mm
	12.5mm
	15mm

Software

OS Compatibility	OS independent; No software or drivers required
------------------	-------------------------------------------------

Environmental

Operating Temperature	0C to 55C (23F to 95F)
Storage Temperature	-20C to 55C (-4F to 131F)
Humidity	5%~65% RH

Physical Characteristics

Color	Black & Silver
Material	Steel and Plastic



Max Drive Height	0.6 in [15 mm]
Product Length	4.7 in [11.9 cm]
Product Width	2.8 in [70.0 mm]
Product Height	0.7 in [16.9 mm]
Weight of Product	3.2 oz [90.0 g]

Packaging Information

Package Length	5.0 in [12.8 cm]
Package Width	3.1 in [78.0 mm]
Package Height	1.0 in [26.0 mm]
Shipping (Package) Weight	4.2 oz [118.0 g]

What's in the Box

Included in Package	2.5" hot swap hard drive tray
	screws
	keys

****Product appearance and specifications are subject to change without notice.***

