

6ft (1.8m) USB-A to B Cable, Universal USB 2.0 Cable, 480Mbps, M/M, TAA Compliant

Product ID: SKUSBAB06-TAA



This USB-A to B cable is purpose-built to deliver secure, reliable, and universal connectivity across a wide range of environments and devices.

Designed for seamless use with our secure KVM switches, this cable ensures stable connectivity and dependable performance in high-security environments. Its TAA-compliant construction makes it ideal for defense operations, healthcare facilities, and command centers, where secure and consistent performance is essential.

The cable works across all major operating systems, including Windows, macOS, ChromeOS, and Linux, and is compatible with all hardware platforms such as Intel, AMD, and Apple Silicon. It has been rigorously tested in an in-house Innovation Lab to ensure durable construction, broad compatibility, and reliable performance.

Certifications, Reports and Compatibility



Applications

- TAA-compliant USB cable is ideal for command centers, defense operations, and healthcare facilities
- Connect a USB-B 2.0 device, such as a Secure KVM, to a USB-A host

Features

- **USB-A to B Connectivity**: Connect a computer or laptop with a USB-A port to a USB-B device such as a printer, scanner, or secure KVM switch; Ideal for reliable data transfer in office, home, or studio setups

- **Purpose-Built for Secure KVMs**: Specifically engineered for seamless integration with our Secure KVM Switches, ensuring stable connectivity and reliable performance in high-security environments, reducing downtime and keeping systems running smoothly
- **Universal Cable**: Works with all secure KVMs that require USB 2.0 connectivity; OS independent, supporting all operating systems including Windows, macOS, ChromeOS, and Linux; Compatible with all hardware platforms such as Intel, AMD, and Apple Silicon
- **TAA-Compliant**: Engineered for secure, reliable performance in mission-critical environments, these cables are ideal for command centers, defense operations, and healthcare facilities, ensuring seamless connectivity where it matters most
- **The IT Pro's Choice**: Our cables are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and broad compatibility with a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

Performance

Warranty	2 Years
Maximum Data Transfer Rate	480Mbps

Physical Characteristics

Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.1 in [29 mm]
Product Height	0.2 in [6 mm]
Weight of Product	0.2 lb [0.1 kg]

Packaging Information

Package Length	5.4 in [13.8 cm]
Package Width	15.6 in [39.5 cm]
Package Height	2.0 in [5.1 cm]
Shipping (Package) Weight	4.8 oz [135.0 g]

****Product appearance and specifications are subject to change without notice.***